

## Features

- Ultra high input resistance, typically  $5 \times 10^{10} \Omega$ .
- Frequency response (-3dB) 50mHz to 20kHz.
- Wide operating voltage from 4.0 to 8.0V.
- Operating temperature range 0 to 50°C.
- 200pF load drive capability.
- Ground referenced output.
- DC signal rejection.
- Dual sensor board allows differential operation.

## Applications

- Electrophysiological signal detection.
  - ECG/EOG/EMG/EEG
- Electric field and potential sensing.
  - Movement sensing




Figure 1: PS25012A4 single channel board carrying a single PS25204 sensor




Figure 2: PS25012B4 dual channel board carrying two PS25204 sensors

## Description

The PS25012A4 and PS25012B4 are single and dual channel application boards for the demonstration of the Plessey PS25204 electric potential sensor.

The PS25204 electric potential sensors on these boards allow the measurement of a wide range of electric potential sources from electrophysiological signals through to spatial electric field. The sensors incorporate a DC block feature that allows the DC component of an applied signal to be rejected while maintaining good low frequency response. The electrode surface of the detector is passivated with a thin dielectric that allows the direct application to a test surface. In the case of contact with skin there is no need for electrically conductive gel.

The PS25204 sensor demonstrated on these boards is an integrated assembly designed for surface mount assembly on a motherboard.

The application boards provide the regulated +2.5V and generated -2.5V supplies that are used to operate the sensor. This allows the boards to demonstrate the sensors from a wide, single sided, power supply voltage while the output of the sensor can cover the range  $\pm 2.1V$ . The boards are connected by a high reliability five pin connector.

Two single channel PS25012A4 boards or a dual channel PS25012B4 board may be used to generate a differential signal. A typical example is shown in Figure 3 below:




Figure 3: Differential signal from two sensors in contact with the skin showing ECG type characteristics

**Electrical Characteristics**


These electrical characteristics apply to the PS25012A4 and PS25012B4 application boards that carry the PS25204 sensors. The electrical characteristics (@25°C) are guaranteed by either production test or by design and characterisation. They apply within the specified supply voltage unless otherwise stated.

| Characteristics           | Value |      |      | Units | Conditions/Notes   |
|---------------------------|-------|------|------|-------|--|
|                           | Min.  | Typ. | Max. |       |  |
| Supply voltage            | 4.0   |      | 8.0  | V     | Each PS25204 sensor consumes 2.0mA (typ). The additional current is consumed by the app'n board.<br><br>Sensor to skin |
| Supply current; PS25012A4 | 2.7   |      | 10.0 | mA    |  |
| Supply current; PS25012B4 | 5.4   |      | 20.0 | mA    |  |
| Input resistance (Rin)    |       | 50   |      | GΩ    |  |
| Input capacitance         |       | 10   |      | pF    |  |
| Voltage Gain (Av)         |       | 10   |      |       |  |
| Coupling capacitance      |       | 250  |      | pF    |  |
| Lower -3dB point          |       | 0.05 |      | Hz    |  |
| Upper -3dB point          |       | 20.0 |      | kHz   |  |
| Noise                     |       | tdb  |      |       |  |

**Electrical Connector**

The PS25012A4 and PS25012B4 application boards are fitted with one or two five pin sockets. The connectivity of these sockets is shown below:

- Pin 1 Output
- Pin 2 Gnd
- Pin 3 Supply
- Pin 4 Gnd
- Pin 5 Not used



The supply and ground connections of the two sockets on the dual channel PS25012B4 board are connected in parallel so that the board will be active with either one or both connectors in use. However, when both sockets are powered the supplied voltages must be identical.

**Auxiliary Components**

- PS25000A Control and Interface Box; 50Hz.  
This box provides power for one or two sensors. It incorporates switchable low pass and 50Hz notch filters. The box contains an amplifier with switchable gain of either x1 or x10. The box also generates a differential signal from two sensors. The box incorporates a data acquisition card that provides the data from the sensors via a USB cable to a computer. The box is powered by the USB connection. A soft scope is provided with this box for display of the signals on a computer.
- PS25001A Control and Interface Box; 60Hz.  
This box is identical to the PS25000A except that the switchable notch filter is preset to reject 60Hz.
- PS25013 Adapter cable.  
This 1.5m long cable connects the sockets of the PS25012A4 and PS25012B4 application boards to the PS25000A or PS25001A Control and Interface Box.

**For further information about this and other products, please visit:  
[www.plesseysemiconductors.com](http://www.plesseysemiconductors.com)**

Data Sheet 291504 Issue 1

Plessey Semiconductors Ltd.  
Design & Technology Centre, Delta 500, Delta Business Park, Great Western Way, Swindon, UK SN5 7XE  
Tel: +44 1793 518000 Fax: +44 1793 518030 Web: [www.plesseysemi.com](http://www.plesseysemi.com)

## Legal Notice

Product information provided by Plessey Semiconductors Limited ("Plessey") in this document is believed to be correct and accurate. Plessey reserves the right to change/correct the specifications and other data or information relating to products without notice but Plessey accepts no liability for errors that may appear in this document, howsoever occurring, or liability arising from the use or application of any information or data provided herein. Neither the supply of such information, nor the purchase or use of products conveys any licence or permission under patent, copyright, trademark or other intellectual property right of Plessey or third parties.

Products sold by Plessey are subject to its standard Terms and Conditions of Sale that are available on request. No warranty is given that products do not infringe the intellectual property rights of third parties, and furthermore, the use of products in certain ways or in combination with Plessey, or non-Plessey furnished equipments/components may infringe intellectual property rights of Plessey.

The purpose of this document is to provide information only and it may not be used, applied or reproduced (in whole or in part) for any purpose nor be taken as a representation relating to the products in question. No warranty or guarantee express or implied is made concerning the capability, performance or suitability of any product, and information concerning possible applications or methods of use is provided for guidance only and not as a recommendation. The user is solely responsible for determining the performance and suitability of the product in any application and checking that any specification or data it seeks to rely on has not been superseded.

Products are intended for normal commercial applications. For applications requiring unusual environmental requirements, extended temperature range, or high reliability capability (e.g. military, or medical applications), special processing/testing/conditions of sale may be available on application to Plessey.