EMEME Micro-Measurements



Gage Installation Tester



FEATURES

- A compact, battery-powered instrument used to verify the electrical quality of a strain gage installation BEFORE it is placed in service
- Reads with the push of a button no warm-up
- Reads insulation resistance (leakage) to 20,000 megohms with 15Vdc
- Measures deviation of installed gage resistance from precise standards to a resolution of 0.02 percent
- Ohmmeter scale for troubleshooting questionable installations
- · Verifies the complete gage circuit, including leadwires

DESCRIPTION

Two of the most important measurements used to verify the quality of a strain gage installation are insulation resistance (leakage to ground) and shift in gage resistance due to installation procedures. While these two measurements are not a complete guarantee of eventual proper strain gage performance, any installation that produces questionable values should not be relied upon where accuracy of results is necessary.

For example, a voltage difference between the specimen and strain gage frequently exists. A low insulation resistance will permit this voltage differential to introduce extraneous signals during strain measurement.

Several sources of variations in insulation resistance and shifts in gage resistance are:

 Insulation resistance in excess of 20,000 megohms should be expected for foil strain gages when installed under laboratory conditions. A value of 10,000 megohms should be considered minimum. A reading below this value generally indicates trapped foreign matter, moisture, residual flux or backing damage due to soldering, as well as incomplete solvent evaporation from an overcoating.

- Deterioration of the insulation resistance with time may be an indication of an improperly coated installation.
- At higher test temperatures, particularly above +300°F [+150°C], it is normal to expect lesser values. Ten megohms is considered to be the lower allowable value.
- Shifts in gage resistance during installation should not normally exceed 0.5% when using room-temperature-curing adhesives. Resistance shifts greater than 0.5% generally indicate damage to the gage due to improper handling or clamping. However, strain gages installed using elevated-temperature-curing adhesives may exhibit greater shifts in resistance due to adhesive lock-up at elevated temperatures (difference in linear coefficient of thermal expansion between the strain gage and specimen). These shifts will vary depending upon the specific cure temperature and materials used. The shifts should never exceed 2% and should be uniform within 0.5%.

For technical questions, contact: micro-measurements@vishaypg.com

Document Number: 11301

Revision: 28-Jun-10



Micro-Measurements **EMEM**

Gage Installation Tester

SPECIFICATIONS

Input Circuits:

Gages: Three-wire quarter bridge (120Ω and 350Ω) and half bridge. Other value quarter bridges using customer's reference, at readily accessible panel terminals.

As ohmmeter: Two leads $(500\Omega \text{ and } 500\text{M}\Omega \text{ midscale})$.

Input Leads:

4-ft [1.2m] 4-conductor AWG #26 [0.4-mm diameter] twisted Teflon®-insulated cable supplied (with ground clip and three tinned leads).

Meter:

3.5-in size (3.00-in [76-mm] scale length) with mirror. Tracking accuracy $\pm 1\%$ full range.

Mode Switch:

Five momentary push buttons: battery check, $\pm 5\%$ deviation, $\pm 1\%$ deviation, gage resistance (ohms), and insulation resistance (megohms).

Deviation Mode:

Two ranges, $\pm 1\%$ and $\pm 5\%$, F.S. (50 graduations either side of zero).

Accuracy:

1% range: 0.04% ΔR (2 meter graduations) 5% range: 0.2% ΔR (2 meter graduations)

Excitation: 1.0Vdc per gage.

Insulation Resistance Mode:

Graduated 5M Ω to 20,000M Ω (500M Ω mid-scale).

Accuracy: 1 scale division.

Test Voltage: 15Vdc open circuit.

Ohm Mode:

Graduated 5Ω to $20k\Omega$ (500Ω mid-scale).

Accuracy: 1 scale division.

Test Voltage: 2Vdc open circuit (0.4Vdc @ 120Ω).

Environmental:

+15° to +125°F [-10° to +50°C]; up to 80% relative humidity, non-condensing.

Size:

Aluminum case (separable lid) $5 H \times 7 W \times 5 D$ in with lid [125 x 180 x 126mm].

Weight:

3.6lb [1.6kg] with batteries.

Power Supply:

Four 9V NEDA 1604 batteries (Eveready® 216 or equivalent).

Life: Will fully test 1000-5000 installations.

All specifications are nominal or typical @ +23°C unless noted.

Teflon is a Registered Trademark of DuPont

Eveready is a Registered Trademark of Eveready Battery Co Inc.



Legal Disclaimer Notice



Vishay Precision Group

Disclaimer

All product specifications and data are subject to change without notice.

Vishay Precision Group, Inc., its affiliates, agents, and employees, and all persons acting on its or their behalf (collectively, "Vishay Precision Group"), disclaim any and all liability for any errors, inaccuracies or incompleteness contained herein or in any other disclosure relating to any product.

Vishay Precision Group disclaims any and all liability arising out of the use or application of any product described herein or of any information provided herein to the maximum extent permitted by law. The product specifications do not expand or otherwise modify Vishay Precision Group's terms and conditions of purchase, including but not limited to the warranty expressed therein, which apply to these products.

No license, express or implied, by estoppel or otherwise, to any intellectual property rights is granted by this document or by any conduct of Vishay Precision Group.

The products shown herein are not designed for use in medical, life-saving, or life-sustaining applications unless otherwise expressly indicated. Customers using or selling Vishay Precision Group products not expressly indicated for use in such applications do so entirely at their own risk and agree to fully indemnify Vishay Precision Group for any damages arising or resulting from such use or sale. Please contact authorized Vishay Precision Group personnel to obtain written terms and conditions regarding products designed for such applications.

Product names and markings noted herein may be trademarks of their respective owners.

Document Number: 63999 www.vishaypg.com Revision: 22-Feb-10