

Stress Analysis Gages

GAGE SELECTION

Many factors, such as test duration, strain range required, and operating temperature, must be considered in selecting the best strain gage/adhesive combination for a given test profile. These factors and others are addressed in Tech Note TN-505, "Strain Gage Selection — Criteria, Procedures, Recommendations."

SELF-TEMPERATURE COMPENSATION (S-T-C)

All gages with XX as the second code group in the gage designation are self-temperature-compensated for use on structural materials with specific thermal expansion

S-T-C NO.	EXPANSION COEFFICIENTS**		COMMON
	per °F	per °C	MATERIAL
00	0.8	1.4	Invar, Fe-Ni alloy
	0.3	0.5	Quartz, fused
	0.0	1.4	Titanium Silicate*, polycrystalline
03	3.0	5.4	Alumina, fired
	2.7	4.9	Molybdenum*, pure
	2.4	4.3	Tungsten, pure
	3.1	5.6	Zirconium. pure
05	5.1	9.2	Glass, Soda-Lime-Silica
	5.5	9.9	Stainless Steel, Ferritic (410)
	4.8	8.6	Titanium, pure
	4.9	8.8	Titanium Alloy, 6Al-4V*
06	6.4	11.5	Beryllium, pure
	6.0	10.8	Cast Iron, grey
	7.0	12.6	Inconel, Ni-Cr-Fe alloy
	6.7	12.1	Inconel X, Ni-Cr-Fe alloy
	7.5	13.5	Monel, Ni-Cu alloy
	6.6	11.9	Nickel-A, Cu-Zn-Ni alloy
	6.3	11.3	Steel alloy, 4340
	6.7	12.1	Steel, Carbon, 1008, 1018*
	6.0	10.8	Steel, Stainless,
			Age Hardenable (17-4PH)
	5.7	10.3	Steel, Stainless,
			Age Hardenable (17-7PH)
	5.0	9.0	Steel, Stainless,
			Age Hardenable (PH15-7Mo)
09	9.3	16.7	Beryllium Copper, Cu 75, BE 25
	10.2	18.4	Bronze, Phosphor, Cu 90, Sn 10
	9.2	16.5	Copper, pure
	9.6	17.3	Steel, Stainless, Austenitic (304*)
	8.0	14.4	Steel, Stainless, Austenitic (310)
	8.9	16.0	Steel, Stainless, Austenitic (316)
13	12.9	23.2	Aluminum Alloy, 2024-T4*,
	11.1	20.0	7075 T6; Brass, Cartridge,
	13.0	23.4	Cu 70-Zn 30; Tin, pure
15	14.5	26.1	Magnesium Alloy*, AZ-318

^{*} Indicates type of material used in determining thermal output curves supplied with Micro-Measurements strain gages.

coefficients. The table below lists S-T-C numbers and test specimen materials to which gages are thermally matched.

When ordering, replace the XX code group with the desired S-T-C number, which is the approximate thermal expansion coefficient of the structural material in ppm/°F. The Gage Designation System lists the available S-T-C numbers for specific grid alloys. The 06 and 13 values, available in A and K alloys, are most common and more likely to be in stock. When not otherwise specified, the 06 compensation is shipped.

GAGE RESISTANCE

Micro-Measurements strain gages are available in various resistance values that range from 30 to 5000 ohms.

Strain gages with resistances of 120 and 350 ohms are commonly used in experimental stress analysis testing. For the majority of applications, 120-ohm gages are usually suitable; 350-ohm gages would be preferred to reduce heat generation (for the same applied voltage across the gage), to decrease leadwire effects, or to improve signal-to-noise ratios in the gage circuit. Higher resistance gages are typically used in transducer applications and on composite materials.

GAGE FACTOR

Gage Factor (GF) is the measure of sensitivity, or *output*, produced by a resistance strain gage. Gage factor is determined through calibration of the specific gage type, and is the ratio between $\Delta R/R_o$ and $\Delta L/L$ (strain), where R_o is the initial unstrained resistance of the gage. It is affected somewhat by pattern size, geometry, S-T-C number, and temperature. Each gage package is supplied with the GF as well as its tolerance and temperature sensitivity. Nominal gage factors for various alloys are: A = 2.05; K = 2.1; D = 3.2; P = 2.00.

TRANSVERSE SENSITIVITY

All gages are sensitive, to some degree, to strains transverse to the grid direction. The transverse sensitivity factor (K_1) is given with the engineering data supplied with all gage types for which the data is relevant.

STRAIN GAGE ADHESIVE SELECTION

When selecting a strain gage, it is most important to consider the adhesive that will be used to bond the gage, since the adhesive becomes part of the gage system and correspondingly affects the performance of the gage. However, when the interaction of test characteristics becomes too complex for selecting the gage/adhesive combination in a straight forward manner, contact our Applications Engineering Department for recommendations.

^{**} Nominal values at or near room temperature for temperature coefficient of expansion values.

EMEME Micro-Measurements



Stress Analysis Gages

CUSTOM GAGES

Unusual applications occasionally require a strain gage which is neither listed in the catalog nor available by adding special optional features. Often a custom product can be designed to fit such needs.

Careful consideration is given to the backing, foil, S-T-C, gage length, pattern, resistance and resistance tolerance, operating temperature range, test duration, maximum strain, cyclic endurance, leads, encapsulation, and trim so that the custom gage is designed to properly meet the user's needs.

Examples of custom gages include such features as unusual patterns, special trim dimensions, and nonstandard lead materials or length.

A special part number is normally assigned to each custom gage. Doing so ensures that the correct gage is produced each time it is ordered. A set-up charge and a minimum order will normally apply. For further information contact our Applications Engineering Department.



SUPER STOCK GAGES AND SENSORS

At our facility in Raleigh, North Carolina, we maintain a stock of the most commonly used gages listed in this catalog. These gages are often in stock for immediate delivery. Inventory levels of gages in Super Stock strain gages are revised to reflect changes in gage usage by our customers, and are subject to change from time to time.

RAPID RESPONSE GAGES AND SENSORS

Another group of somewhat less commonly ordered gages and sensors sometimes may also be available from stock. Should either a Super Stock or Rapid Response gage be unavailable from stock, they can be produced to order with specially reduced lead times.

STOCK STATUS

To determine the quantities of all gages and sensors currently available from stock, please contact either our Customer Service Department or our sales representative in your area.

ORDERING REQUIRMENTS

ORDER MULTIPLES

All gages must be ordered in the multiples of the number of pieces per package as shown on the price list. For packages with 5 gages each, for example, the order multiples are 5, 10, 15, etc.

MINIMUM ORDER REQUIREMENTS

Super Stock and Rapid Response Gages & SensorsIf gages on either the Super Stock or Rapid Response list are ordered, a minimum order requirement never applies.

Other Gages & Sensors Available From Stock

If gages other than those on the Super Stock and Rapid Response lists are ordered and are in stock in the ordered quantity, a minimum order requirement never applies.

Other Gages & Sensors Unavailable From Stock

If gages other than those on the Super Stock and Rapid Response lists are ordered and are not available from stock in the ordered quantity, a minimum order requirement applies.

Gages on the Super Stock and Rapid Response lists, as well as those subject to MOR, are subject to change. Please contact our Customer Service Department to determine if an MOR is applicable to your order.

For technical questions, contact: micro-measurements@vishaypg.com

Document Number: 11504

Revision: 28-Jan-10

Legal Disclaimer Notice



Vishay Precision Group

Disclaimer

All product specifications and data are subject to change without notice.

Vishay Precision Group, Inc., its affiliates, agents, and employees, and all persons acting on its or their behalf (collectively, "Vishay Precision Group"), disclaim any and all liability for any errors, inaccuracies or incompleteness contained herein or in any other disclosure relating to any product.

Vishay Precision Group disclaims any and all liability arising out of the use or application of any product described herein or of any information provided herein to the maximum extent permitted by law. The product specifications do not expand or otherwise modify Vishay Precision Group's terms and conditions of purchase, including but not limited to the warranty expressed therein, which apply to these products.

No license, express or implied, by estoppel or otherwise, to any intellectual property rights is granted by this document or by any conduct of Vishay Precision Group.

The products shown herein are not designed for use in medical, life-saving, or life-sustaining applications unless otherwise expressly indicated. Customers using or selling Vishay Precision Group products not expressly indicated for use in such applications do so entirely at their own risk and agree to fully indemnify Vishay Precision Group for any damages arising or resulting from such use or sale. Please contact authorized Vishay Precision Group personnel to obtain written terms and conditions regarding products designed for such applications.

Product names and markings noted herein may be trademarks of their respective owners.

Document Number: 63999 www.vishaypg.com Revision: 22-Feb-10