

## StrainSmart® Data Acquisition System



### FEATURES

- From 1 to 1200 input channels
- Individual input cards for strain gage and strain-gage-based transducers (Model 6010A), thermocouples (Model 6020), sensors with high-level voltage outputs (Model 6030A), LVDT's (Model 6040A), piezoelectric sensors (Model 6050), and digital tachometer (Model 6095)
- Built-in bridge completion for 120-, 350-, and 1000-ohm strain gages
- Maximum scan rate of 10 000 samples per second per channel; maximum throughput of 200 000 samples per second
- Simultaneous sampling with anti-aliasing filter and analog-to-digital conversion for each channel
- Stable, accurate, low-noise signal conditioning
- Selectable digital filtering of measurement signals
- High-speed PCI hardware interface (Model 6100) and Ethernet network interface (Model 6200A)
- Digital I/O for triggering external events

### DESCRIPTION

System 6000 features data acquisition rates of up to 10,000 samples per second per channel. The hardware is designed to incorporate all the features required for precision strain measurement under a variety of loading conditions, while maintaining flexibility and ease of use. A system can be configured with 1 to 1200 sensors. Strain gages, strain-gage-based transducers, thermocouples, LVDT's, potentiometers, accelerometers, piezoelectric sensors and other transducers can be intermixed by choosing the appropriate sensor card. All System 6000 components can be easily configured for each test requirement. Both the Model 6100 Scanner (holding up to 20 input cards) and the Model 6200A Scanner (holding up to 16 input cards) function independently. Additionally, the smaller, lighter, portable Model 6200A can operate from a variety of dc power sources, and can be configured to remotely perform data acquisition and storage.

Utilizing the benefits of individual analog-to-digital conversion on each channel and simultaneous sampling data acquisition for all channels, System 6000's Model 6100 Scanners record test data at rates of up to 10,000 samples per second per channel of instrumentation hardware. The PCI hardware interface between the scanners and a PC running Strain-Smart software in the Windows NT/2000/XP environment enables a combined throughput of up to 200 000 samples per second for all channels (for example, 20 channels at 10 000 samples per second per channel or 40 channels at 5000 samples per second per channel).

Selectable, digital FIR low-pass filtering is incorporated into each instrumentation channel to meet a variety of testing requirements. Custom filters are also available.

## StrainSmart® Data Acquisition System

### MODEL 6100 SCANNER SPECIFICATIONS



- AC powered
- 19-in rack-mountable, 3.5-in high package
- Accepts up to 20 plug-in input cards
- Support high-speed data transfer and setup of the plug-in cards
- Supports local diagnostics
- Supports software identification and setup of each type of plug-in card

**OPERATION:**

Direct software control.

**INPUTS:**

Accepts up to 20 cards (one channel per card and up to 20 channels per unit).

**SYNC:** Automatic

**DATA STORAGE:** None.

**INTERFACE:** Proprietary PCI.

**SIZE:**

3.5 H x 19 W x 16 D in ( 89 x 483 x 381mm )

**WEIGHT:**


17lb (7.7kg ) empty

19.5lb (8.8kg ) loaded with 20 plug-in cards

**POWER:**

115 or 230Vac user-selectable;  $\pm 10\%$  of setting; 50/60Hz; 200W max.

### MODEL 6200A SCANNER SPECIFICATIONS



- DC powered (AC optional)
- Compact package
- Accepts up to 16 plug-in input cards
- Supports network communication via a 100BASE-T Ethernet connection
- Multiple units can be linked together to provide common control and synchronous sampling
- Offers user-selectable decimal-based (radix 10) and binary-based (radix 2) scanning rates
- On-board program and data storage
- Supports local diagnostics
- Supports software identification and setup of each type of plug-in card

**OPERATION:**

Stand-alone or direct software control.

**INPUTS:**

Accepts up to 16 cards (one channel per card and up to 16 channels per unit).

**SYNC:** Multiple scanners synchronized with synchronization cable links.

**DATA STORAGE:**

Can be configured:

Internal: 2GB solid state.

Removable: ATA form factor removable storage devices, solid state.

**INTERFACE:** Type : Ethernet

Topology : 100Base-T

Protocol : TCP/IP (HTTP)

**OPERATING VIBRATION:**

6G peak in all three axes. Sweep to 10Hz (solid state media).

**OPERATING SHOCK:**

20G peak in all three axes, 5 shocks in each axis (solid state media).

**SIZE:**

4 H x 10 W x 12.3 D in (102 x 254 x 312mm)

**WEIGHT:**


9.1lb (4.1kg) empty, 11.1lb (5.0kg) loaded with 16 plug-in cards.

**POWER:**


Designed for use with dc power; 9-32Vdc, 100W max. Optional power adapter (Model 6207); 120/240Vac.

## StrainSmart® Data Acquisition System

## SENSOR CARD SPECIFICATIONS



## MODEL 6010A STRAIN GAGE CARD



- Supports software identification and setup of each type of plug-in card
- Complete strain gage signal conditioner with 16-bit analog-to-digital converter
- Programmable digital filter
- Programmable excitation supply per channel. The supply is settable to 0, 0.5, 1, 2, 5, and 10V. Up to 50mA of excitation current is available on each channel. Remote sense is provided for full-bridge transducers.
- Programmable gain to complement the excitation steps of 1, 2, 5, and 10V. Full-scale input range will be  $\pm 16\ 383\ \mu\epsilon$ . An excitation setting of 0.5V will use the 1V gain range, but with one-half the resolution. Gain settings are independent per channel.
- Internal bridge completion resistors: 120 $\Omega$ , 350 $\Omega$ , and 1000 $\Omega$  dummy resistors (jumper selectable); 1000 internal half bridge
- Programmable coarse balance range of  $\pm 16\ 300\ \mu\epsilon$  (4096 $\mu\epsilon$  steps)

- Fixed low-pass anti-aliasing filter (six-pole)
- Two programmable shunt calibration circuits
- Input connections to user's strain gage via nine-pin D-sub connector

**CHANNELS:** One per card.

**INPUTS:****Strain Gages:**

120 $\Omega$ , 350 $\Omega$ , 1000 $\Omega$  quarter bridges; 60 $\Omega$  to 5000 $\Omega$  half and full bridges.  
Jumper-selectable completion resistors (0.01%  $\pm$  2.5ppm/ $^{\circ}$ C typical).

**Measurement Range:**

Normal range mode:  $\pm 16\ 380\ \mu\epsilon$   
High range mode:  $\pm 163\ 800\ \mu\epsilon$   
Low range mode:  $\pm 1638\ \mu\epsilon$

**Resolution:**

Normal range mode: 0.5 $\mu\epsilon$   
High range mode: 5 $\mu\epsilon$   
Low range mode: 0.05 $\mu\epsilon$

**Strain Gage Based Transducers:**

60 $\Omega$  to 5000 $\Omega$  impedance

**Measurement Range:**

Normal range mode:  $\pm 8\text{mV/V}$   
High range mode:  $\pm 80\text{mV/V}$   
Low range mode:  $\pm 0.8\text{mV/V}$

**Resolution:**

Normal range mode: 0.25 $\mu\text{V/V}$   
High range mode: 2.5 $\mu\text{V/V}$   
Low range mode: 0.025 $\mu\text{V/V}$

**Input Impedance:**

220M $\Omega$  each input.

**Source Current:**  $\pm 25\text{nA}$  max.

Input Connector: Nine-pin D-sub style.

StrainSmart® Data Acquisition System

**AMPLIFIER:**

**Zero Temperature Stability:**

±1.5µV/°C RTI, ±100µV/°C RTO, after 30-minute warm-up.

**DC Gain Accuracy & Stability:**

(±0.1% at 23°C) ±50ppm/°C

**Common-Mode Rejection (dc to 60Hz):**

100dB typical

**Common-Mode Voltage:**

±6V typical

**AC Accuracy: (typical):**

Input Frequency/Bandwidth:	500/3000	50/200
Spurious Free Dynamic Range:	100dB	110dB
Signal to Noise:	90dB	95dB
Signal to Distortion:	100dB	110dB

**Coarse Balance Range:**

±99% of measurement range (typically ±16 300µε)

**CALIBRATION:**

Two shunt calibration points are available on each channel. Switch-selectable.

Calibration switches, A and B, are software selectable.

**EXCITATION:**

0.0, 0.5, 1.0, 2.0, 5.0, and 10.0Vdc. Software-programmable.

**Accuracy:**

±3mV typical

**Current:**

50mA max. Over-current protected.

**Load Regulation:**

<0.05% of full scale for a load variation of 10% to 100% of full load

**Temperature Stability:**

Better than ±0.005%/°C

**Remote Sense:**

15Ω maximum lead resistance.

**A/D CONVERTER :**

**Type:**

16-bit successive approximation with integrated sample and hold.

**Integral Linearity Error:**

±2 LSB

**FILTERS:**

Linear phase, analog, 6-pole anti-aliasing filter, and 256-tap, programmable, FIR digital filter (lowpass)

**Passband Frequency:**

User-selectable 1Hz to 4kHz

**ANALOG OUTPUT: (6010A version only)**

**Type:**

±5.00V max for typical full-scale input of ±16 380µε


**Output Load:**

2000Ω min

**Bandwidth:**

DC to 15kHz (-0.5dB typical)

**MODEL 6020A THERMOCOUPLE CARD**



- Complete thermocouple signal conditioner with 16-bit analog-to-digital converter
- Programmable digital filter
- Programmable common cold-junction reference
- Compensation is provided for J, K, T, N, E, R, S, and B thermocouple types
- Fixed low-pass anti-aliasing filter (six-pole)
- Connections to user's thermocouple circuit via a removable three-terminal screw connector

**CHANNELS:** One per card.

**INPUTS:**

Thermocouple types J, K, T, E, N, R, S, B. Built-in electronic cold-junction compensation. Software-selectable

Open sensor detection

**Input Impedance:** 10MΩ differential, 100KΩ common mode.

**Source Current:** ±0.5nA typical; ±5nA max.

**INPUT CONNECTOR:** Three-position screw terminal

**AMPLIFIER:**

**Zero Temperature Stability:**

±1.5µV/°C RTI, ±100µV/°C RTO, after 30-minute warm-up.

**DC Gain Accuracy & Stability:**

0.05% at 23°C ± 50ppm/°C

**Common-Mode Rejection (dc to 60Hz):**

100dB typical

**Common-Mode Voltage:**

±6V typical

## StrainSmart® Data Acquisition System

**AC Accuracy: (typical):**

Input Frequency/Bandwidth:	500/3000	50/200
Spurious Free Dynamic Range:	100dB	110dB
Signal to Noise:	90dB	95dB
Signal to Distortion:	100dB	110dB

**MEASUREMENT RANGE:** ±81.9mV**RESOLUTION:** 2.5µV**A/D CONVERTER :****Type:**

16-bit successive approximation with integrated sample and hold.

**Integral Linearity Error:**


±2 LSB

**FILTERS:**

Linear phase, analog, 6-pole anti-aliasing filter, and 256-tap, programmable, FIR digital filter (lowpass)

Passband Frequency:

User-selectable 1Hz to 4kHz

**MODEL 6030A HIGH-LEVEL INPUT CARD**

- Complete high-level signal conditioner with 16-bit analog-to-digital converter
- Programmable gain
- Programmable digital filter
- Programmable excitation supply. The supply is settable to 0, 0.5, 1, 2, 5, 10, 15, 20, 24, and 30V. Up to 50mA of current is available on each channel.
- Fixed low-pass anti-aliasing filter (six-pole)
- Input connections to user's voltage source via nine-pin D-sub connector
- Analog output

**CHANNELS:** One per card.**INPUTS:** DC volts (differential)**Input Impedance:** 22MΩ each input.**Source Current:** ±2nA typical; ±100nA max**INPUT CONNECTOR:** Nine-pin D-sub style**AMPLIFIER:****Zero Temperature Stability:**

±2µV/°C RTI, typical. ±100µV/°C RTO, after 30-minute warm-up.

**DC Gain Accuracy & Stability:**

±0.05% at 23°C ± 20ppm/°C

**Common-Mode Rejection (dc to 60Hz):**

86dB typical at X1 gain

94dB typical at X10 gain

**Common-Mode Voltage:**

±12V typical

**AC Accuracy: (typical):**

Input Frequency/Bandwidth:	500/3000	50/200
Spurious Free Dynamic Range:	100dB	110dB
Signal to Noise:	90dB	95dB
Signal to Distortion:	100dB	110dB

**MEASUREMENT RANGES:** ±1, ±2, ±5, ±10Vdc**RESOLUTION:** 30.5, 61, 152.5, 305µV**EXCITATION:**

0, 0.5, 1.0, 2.0, 5.0, 10.0, 15.0, 20.0, 24.0, 30.0Vdc

**Accuracy:**

±10mV typical at 0 to 24Vdc; ±5% at 30Vdc

**Current:**

50mA max. Over-current protected

Over-current protected.

**Load Regulation:**

&lt;±0.05% of full scale for a load variation of 10% to 100% of full load

**Temperature Stability:**

Better than ±0.005%/°C

**A/D CONVERTER :****Type:**

16-bit successive approximation with integrated sample and hold.

**Integral Linearity Error:**

±2 LSB

**FILTERS:**

Linear phase, analog, 6-pole anti-aliasing filter, and 256-tap, programmable, FIR digital filter (lowpass)

Passband Frequency:

User-selectable 1Hz to 4kHz

**ANALOG OUTPUT: (6030A version only)****Type:**

±5.00V max for typical full-scale input of ±32767µε

**Output Load:**


2000Ω min

**Bandwidth:**

DC to 15kHz (-0.5dB typical)

## StrainSmart® Data Acquisition System

### MODEL 6040A LVDT CARD



- Complete LVDT signal conditioner with 16-bit analog-to-digital converter
- Programmable digital filter
- Independent ac excitation supply
- Programmable gain steps of 1, 2, 5, and 10
- Supports six-, five-, four-, and three-wire transducers
- Fixed low-pass anti-aliasing filter (six-pole)
- Excitation reference provided for calibration
- Input connections to user's transducer via nine-pin D-sub connector

**CHANNELS:** One per card.

**INPUTS:** 3- to 6-wire transducers.

**Input Impedance:** 10M $\Omega$  each input.

**Source Current:**  $\pm 2$ nA typical;  $\pm 100$ nA max

**INPUT CONNECTOR:** Nine-pin D-sub style

**AMPLIFIER:**

**Zero Temperature Stability:**

$\pm 2$  $\mu$ V/ $^{\circ}$ C RTI, typical.  $\pm 100$  $\mu$ V/ $^{\circ}$ C RTO, after 30-minute warm-up.

**Gain Accuracy & Stability:**

$\pm 0.25$ % typical

**Common-Mode Rejection (dc to 60Hz):**

86dB typical at X1 gain

94dB typical at X10 gain

**Common-Mode Voltage:**

$\pm 12$ V typical

**MEASUREMENT RANGES:**  $\pm 0.5$ ,  $\pm 1$ ,  $\pm 2.5$ ,  $\pm 5$ Vrms

**RESOLUTION:** 15.25, 30.5, 76.2, 152.5 $\mu$ Vrms

**CALIBRATION:** Excitation sample

**EXCITATION:**

3.0Vrms at 2500, 5000, or 10000Hz sine wave.

Software-selectable

**Accuracy:**

$\pm 5$ mVrms typical

**Current:**

$\pm 50$ mA max.

Over-current protected.

**Load Regulation:**

$< \pm 0.1$ % of full scale for a load variation of 10% to 100% of full load

**Temperature Stability:**

Better than  $\pm 0.05$ %/ $^{\circ}$ C

**A/D CONVERTER :**

**Type:**

16-bit successive approximation with integrated sample and hold

**Integral Linearity Error:**

$\pm 2$  LSB

**FILTERS:**

Butterworth, six-pole anti-aliasing analog filter, and 256-tap, programmable, FIR digital filter (lowpass)

Passband Frequency:

User-selectable 1Hz to 4kHz


**ANALOG OUTPUT:** (6040A version only)

Linear Output:  $\pm 5.00$ V for typical full-scale input

Output Load: 2000 $\Omega$  min

Bandwidth: DC to 1kHz (-3dB typical)

## StrainSmart® Data Acquisition System

**MODEL 6050 PIEZOELECTRIC CARD**

- Complete piezoelectric signal conditioner with 16-bit analog-to-digital converter
- Supports both VM (voltage mode, low impedance) and CM (charge mode, high impedance) type piezoelectric transducers
- Programmable constant current excitation supply for VM transducers is software settable to 1, 2, 4, 5, 10 and 20mA
- Programmable gain steps of 1, 2, 5, and 10 for VM transducers and steps of 1, 2, 5, 10, 20, 50 and 100 for CM transducers
- Programmable digital filter
- Fixed low-pass anti-aliasing filter (six-pole)
- Input connections to user's transducer via BNC connector

**CHANNELS:** One per card.

**INPUTS:** Voltage mode (VM) or charge mode (CM) piezoelectric type transducers (type is switch-selectable)

**Coupling:**

**CM type** - charge amplifier with software-selectable time constants of 0.5 and 5 seconds

**VM type** - ac coupling to remove dc bias voltage with high pass response of 0.1Hz (-3dB)

**INPUT CONNECTOR:** Female BNC

**AMPLIFIER:****Zero Temperature Stability:**

$\pm 10 \mu\text{V}/^\circ\text{C}$  RTI, typical, after 30-minute warm-up

**Charge Amplifier Zero Stability:**

$\pm 1.2 \text{pC}/^\circ\text{C}$  RTI typical at 0.5 second time constant

**DC Gain Accuracy & Stability:**

$\pm 0.1\%$  at  $+23^\circ\text{C}$ ;  $\pm 25 \text{ppm}/^\circ\text{C}$

**AC Accuracy: (typical at X2 gain step)**

Input Frequency/Bandwidth:	500/3000	50/200
Spurious Free Dynamic Range:	100dB	110dB
Signal to Noise:	90dB	95dB
Signal to Distortion:	100dB	110dB

**MEASUREMENT RANGES:**

VM type transducers:  $\pm 10.5\text{V}$ ,  $\pm 5.25\text{V}$ ,  $\pm 2.1\text{V}$ , and  $\pm 1.05\text{V}$   
 CM type transducers:  $\pm 200\ 000\text{pC}$ ,  $\pm 100\ 000\text{pC}$ ,  
 $\pm 40\ 000\text{pC}$ ,  $\pm 20\ 000\text{pC}$ ,  $\pm 10\ 000\text{pC}$ ,  $\pm 4000\text{pC}$ , and  
 $\pm 2000\text{pC}$

**RESOLUTION:** 0.0015% of range

**CALIBRATION:** Excitation sample

**EXCITATION:**

0, 1, 2, 4, 5, 10 and 20mA selections for VM type transducers

**Accuracy:**

$\pm 1\% + (\pm 30 \mu\text{A})$  typical at 1 to 20mA

**Voltage Compliance:** 0 to 28V.

**Temperature Stability:**

$\pm 50 \text{ppm}/^\circ\text{C}$

**A/D CONVERTER :****Type:**

16-bit successive approximation with integrated sample and hold

**Integral Linearity Error:**

$\pm 2 \text{LSB}$

**FILTERS:**


Linear phase, analog, 6-pole anti-aliasing filter, and 256-tap, programmable, FIR digital filter (lowpass)

**Passband Frequency:**

User-selectable 1Hz to 4kHz

## StrainSmart® Data Acquisition System

### MODEL 6095 DIGITAL/TACHOMETER CARD



**INPUT CONNECTOR:** Nine-pin, D-sub style

**RELAY OUTPUTS:**

**Quantity:** One

**Configuration:** NO and NC, 500mA contact at 30Vac or 30Vdc into resistive load.

**DIGITAL INPUTS:**

**Quantity:** Four

**Configuration:** Optically isolated. TTL Schmitt-trigger input thresholds accept up to 28Vdc without damage. 2.23 $\Omega$  pull-up resistors can be selected for each input.

**Impedance:** 50k $\Omega$

**Data Rate:** DC to 200kHz

**Accessory Supply:** 5 Volt  $\pm$  5%, 75mA

- Multi-function digital input card
- Relay output for control functions
- Compatible with all System 6000 hardware
- Supported by StrainSmart software

When used in conjunction with Micro-Measurements StrainSmart® Software, the Model 6095 Digital/Tachometer Card enables the user to capture and reduce data in any one of five operating modes:

- Tachometer Mode
- Interval Mode
- Quadrature Mode
- Counter Mode
- Digital Input Mode

Depending upon the mode selected, data can be reduced as a digital input; counts; interval counts; pulses; rate; shaft angle; RPM; radians or degrees per second; elapsed time (milliseconds, seconds or minutes); or calculated values.

Multiple Model 6095 Cards can be used in each system, and each card in a system can be configured individually to any operating mode. However, the relay provides one distinct control function (on/off control for testing machines, etc.) per system when using a Model 6100 Scanner, or one per scanner when using multiple Model 6200 Scanners.

The Model 6095 is compatible with all Model 6100 and 6200 Scanners. It is supported by Version 3.0, and later, StrainSmart Software; no-charge upgrades are available upon request.



## Disclaimer

All product specifications and data are subject to change without notice.

Vishay Precision Group, Inc., its affiliates, agents, and employees, and all persons acting on its or their behalf (collectively, "Vishay Precision Group"), disclaim any and all liability for any errors, inaccuracies or incompleteness contained herein or in any other disclosure relating to any product.

Vishay Precision Group disclaims any and all liability arising out of the use or application of any product described herein or of any information provided herein to the maximum extent permitted by law. The product specifications do not expand or otherwise modify Vishay Precision Group's terms and conditions of purchase, including but not limited to the warranty expressed therein, which apply to these products.

No license, express or implied, by estoppel or otherwise, to any intellectual property rights is granted by this document or by any conduct of Vishay Precision Group.

The products shown herein are not designed for use in medical, life-saving, or life-sustaining applications unless otherwise expressly indicated. Customers using or selling Vishay Precision Group products not expressly indicated for use in such applications do so entirely at their own risk and agree to fully indemnify Vishay Precision Group for any damages arising or resulting from such use or sale. Please contact authorized Vishay Precision Group personnel to obtain written terms and conditions regarding products designed for such applications.

Product names and markings noted herein may be trademarks of their respective owners.