



*** NOTE**

$R = 100\Omega$ or 150Ω

Two 100Ω resistors and two 150Ω resistors are included in the kit.

The 100Ω resistors are used for 75Ω input and output.

The 150Ω resistors are used for 50Ω input and output.

**HEATHKIT REFLECTED POWER
AND STANDING WAVE RATIO BRIDGE
MODEL AM-2**

Heathkit

REFLECTED POWER AND S.W.R. BRIDGE

HEATH COMPANY
A DIVISION OF GASTRO

STAYTON HARBOR, MICHIGAN



FUNCTION

SENSITIVITY



FORWARD

REFLECTED

MINIMUM

MAXIMUM



MODEL AM-2