/Inritsu

MP1220A ATM Quality Analyzer

1.5 Mbit/s (T1) to 622 Mbit/s (STM-4c/OC-12c)



For Constructing and Maintaining ATM Networks

The MP1220A is a portable measuring instrument for ATM networks;

it can measure the PDH/SDH physical layer, the ATM layer, and the AAL. It is the perfect instrument for troubleshooting ATM networks during construction and maintenance, and has a wide range of convenient applications in manufacturing inspection of ATM devices.

Features

- Supports various interfaces from 1.5 Mbit/s (T1) to 622 Mbit/s (STM-4c/OC-12c)
- 150 Mbit/s real-time analysis up to CPCS layer
- Simultaneous measurement of two channels (up/down stream)
- Automated inspection measurement of 1023 network channels
- Uses test signals conforming to ITU-T 0.191 recommendations
- 10.4" large color LCD
- Simple touch-panel operation (graphical user interface)
- Portable

Application Examples

Measuring Networks

Monitoring the end-to-end network quality and identifying fault parts are easy. There are three measurement modes for use with all types of interface unit. In the two-way measurement mode, a test signal is impressed on the network, and the error rate, delay time, etc. are measured. In the loopback measurement mode, the received signal is measured during sending, and in the send monitor measurement mode, measurement is performed while monitoring the sent signal.



Measuring Equipment

The various built-in physical interfaces make it easy to test and measure equipment with various interfaces, such as ATM transmission equipment.







Simple Touch-Panel Operation

The MP1220A has a 10.4" TFT color LCD touch panel for simple Graphical User Interface based operation.





- Connector for external monitor
- **2** PS/2 mouse connector
- **3** Keyboard connector
- 4 RS-232C connector (9-pin)
- **6** Connector for external printer
- **6** AC power inlet
- **7** Power switch
- ⁽³⁾ Slot for remote control option
- Slots for expansion units (6 max.)

Graphical User Interface (GUI)

Basic Operations

The MP1220A is operated using the touch-sensitive LCD which is divided into setting and display screens corresponding to each unit.

MP12208 AT	W Deality Analyzer	đ
Die Window View Help Maintenne ISTMI 25Peter STH3 DEB DEM @ P	4 Des	
H	lautane	
//richardson/linearies/linearies/ Synchrongsdoor W noes 1 (HITH-1/07-0 UNIT) W noes 1 (HITH-1/07-0 UNIT) W Stees 1 (HITH-1/07-0 UNIT) W Stees 2 (HITH-1/07-0 UNIT)	Harssenert () Harssenert Sterlig Batton Hitch Record	
SLOT 4 MI	IT20020A GeS UNIT	
Trend and Cell Cell Cell Cell Cell Cell Cell Cell	Background Cel Background Cel 1 USER CELL 1 1.00 2 2 USER CELL 2 2.00 3 USER CELL 3 3.00 4 USER CELL 4 4.00 5	13 13

Screen composition for optional expansion units

Some special setting items have simple and easy-tounderstand screens. In addition, dialog boxes are displayed on-screen during setting to assist with setting details.



Dialog box for setting details

The screen layout is simple even when two screens are displayed simultaneously. And the GUI makes it easy to monitor the measurement results of the ATM layer while adding errors by interface units. Furthermore, screens can be divided in half.

MP1270A ATM Ox	ality Analyzer	
Eile Window Bew Help	and the second second	100
Marrane 27min 1 ATIS 44	Serre Sident	19
		-
- SLITT MUTPHENZA STM-1/SC-3 UNIT -	SLOT & MOTZOZIA GES INCT	-
TC US Screet on Pil Cel (5) Caset on AlamuEmor/Pointer WAtern 1/2 On Etion 10-10 Proces 40, (2) (2)	Emrif Countil SW(Mos) Concerns Count Teer BW (Mos) Countil Teer BW (Mos) Countil Teer BW (Mos) Countil Count Coll Countil Enrored Countil Terred Back Leep Emrout Countil Terred Back Countil Enrored Back Countil	10 H
	ArtingPlask = 200.00004	•

Screen split into left and right halves



Screen split into top and bottom halves

General Settings

The transmitter and receiver can be connected via different interfaces by setting the signal path between different units making it easy to test equipment with different types of interface.

-		1270A ATM G	unity Analyza	t		* *
Maintrama 1514	- grus i	Unit Canned	lian Setup		1	
						*
	E	<u>B</u>	X Care	1		 3

Setting signal path for different units

Any of three measurement methods can be selected: (1) Until the Stop button is pressed after the Start button has been pressed, (2) Automatic measurement stop after a specified time interval has elapsed, and (3) Repeated measurement for a specified period. In addition, the measurement start time can also be set.

	MP1220A A1	M Genilty Analyzet	+ +
	21 30-5 9	Affectes	
There Vortgoder Viet In Synchronization W Dies 1 (278-2000) W Alias 1 (278-7010) W Alias 1 (277-7010) W Alias 4 (278-7010) F There is a second for F There is a second for	Start by Date Time Mode Period	Tanet Made Tanet 4 10707727 2 232 14732 2 109457 4 107076 100	000 1005 1005 1005 1005

Selecting measurement method

A keyboard is displayed on the screen even if an external keyboard is not connected to permit alphanumeric input. Of course, the protective cover with keyboard (sold separately) can also be used for input.

Die Window View Help	MP1270A ATM Genilty Analyzer	1+14
Machanie ISTMI	Charant Schuy 1 12 (19) 1 12 A Fill 2 Pa 3 Pa 4 10 4 VPI 4 VPI 5 VPI 5 VPI 6 VPI 6 VPI 70 10	

Inputting characters from screen

Interface Units

Settings and measurements related to the physical layer, such as addition of various alarms and errors, cell scrambling, and setting empty cell patterns, can be performed.

-	partone espos	MP1220	ATM Genilty Analyzer	
Harbarde	ISTM	r Help 1 artize 1 soc Ale Tope (Forder)	nt (Frank) nnyErroyPointer Setup	
Citers Citers Citers Others	Туре	MS-RDI LOS LOS HS-AIS MJ-AIS HP-RDI LCD	0 1	
Pet	5	J. 0	C X Caccel	

Adding various alarms and errors

the Window York Help	M Guality Analyzer
Mannane (157M) 211/1 205	4Prote 000
HEIDED &	
A SECTION OF A SEC	a (Monto) Provide Harris
TO	AlamiEnor/Printer
Statistic on Carne [5]	Alexa LCD [28]
and the second s	Gun HI-SEI ON
Coset On	@ Parter
	1261
	We have a second se
Alarm	Ema (Court)
· CHEENDE TO LARS	# Cerrent C Laws
ALACE	E
HEED	e)
LCD	MOREI

Simultaneous display of settings and results

The SDH/SONET interface unit can set and monitor the overhead and pointer values.

	MP12286-611	d Guality Analyzer		6
File Mindow Yorw Help		Advaltar Com		
Macrones [1STMI] 21	1/1 3 Gef5	#Fint	CONTRACTOR OF	AD703
	and the second second	fine .	and the second second	Tintest
	35	11 II II		112
-	SLOT 1 (MU12)	1092A STM 1/0C-31	INIT	
And the second second second	Nam/East/Votida	Visions Points History	1	
18 TH C Bulleton TT AT C	mails Trans	- Desider	-	
COLUMN STREET, SAFEL S.	Lach Theorem	- CONTRACT		
S BOM		POH		
AL AL AL AZ AZ	12 (1) (1) (1)			
DI LUC EL CONTRACTOR	81	-		
08 00 00 00 00 1	10.00.00.00	58		
24 00	D0 1	11		
00-00-00-00-00-	10 14 11 11	11		
BIL HI HI HI HE HE I	12 10 10 11	B		
Dr. br. br. bi				
25 42 14 00 00				
24 09	24	24		
00 10 01 00 00	10 29 28 28			
27 00	100	11		
00.140.04.00.4411	10.10.00.00	**		
1310 644	292	10		
at at at he he				
the set of the late	10 10 11 11			

Display of overhead contents

Alarms and errors occurring during measurement can be saved and analyzed using an-easy-to-understand bar graph function. And the analysis function is not restricted to use with the interface units, it can also be used with the QoS and Protocol units.

51. 51.	OT 1 MUT280	BEA STM 1/0C	3 UNIT	n
ngh MI-131		Product If Second Pro-	E BUILD	18.42.78
200			TTT MI-245	79944
100-122 171			403	
			90-410	
				-

Graphical display of alarm/error history



The QoS can set and measure various ATM layer parameters. In addition to being useful for performing measurement using test cells conforming to the ITU-T 0.191 recommendations, other test cells including AAL1, and AAL3/4 can be used.

List of various test cells

The test cells can be generated with various traffic patterns including CBR, burst, sawtooth, Poisson distribution, and manual. In addition to the test cells, up to 10 types of background cells can be output to perform testing under more realistic network conditions.

Treng Paran	*	Lost Dee
10 Saunoorh Cale aith Roma Port External (Port External (Port) External (Port) External (Port)	Day of the constraints of the co	/s Cells/s • 1 mat(71) 1 = class mat(72) 2 = s class s femate 1018 = s Freet) 10 = s to
4		

Various traffic patterns

Furthermore, different items can be measured for each selected test cell.

	MP12286 AT	M Guidily Analyzer		at
Mutes New H	rip	and the second second		-
Mane 15TMI 1 2	11/1 3 OnS	4Fints	- III - 10 5	1211
리킹 다양히 4		204	S line	1
and the state of t	SLOT 9 IN	JI 20025A Quốt UNIT		-
enance Via Sena Via Sen	e / Auntra (Man	e YCapture Settap YCapture Film	4).	_
(Ouunit)		Error(Rate)		
Curr	ant C Leit		Carrent C Last	
W [MEVV]	4,070	EW IVE/VI	4.070	
[and UV/[Mtots]	4.070	Tanat Rov (Mays)	4.070	
MolCol.	115201	Low Cell	F.688-06	
of Cell	1	Encoded Call	D.008-0= 🕥	
around Cell	0.0	Dureiffick	0.002-00 0	
event Cali	1.0			
destified.	111			
mulflock	0.00			
on contents	20			
mailes ato	IL DECEMBER OF			
Nonvine and	And the second s			0
				100
mePust >10	0.10009			

Measurement items for test cells

This unit has a capture function for saving a maximum of 4095 received cells in memory and displaying them. In addition to specifying all cells and cells of specific channels with the capture filter, it is also possible to specify cells where the header byte (GFC, CLP, etc.) and 1st payload byte. OAM cell reception and cell loss errors can be specified as the capture trigger. The capture results can be displayed as hexadecimal code or characters, etc., and can also be translated and displayed. Furthermore, the captured cell-to-cell interval can be displayed.

3004		. In	e On	i.	17		1	-	100	-	-	_	-	1	- 71		1
annen i		1.311	11.0	10	-	runs	1.5	10		-	-	_	1	1	-		91
리는								10		15		12	9		10	-	11
-	-	-	111		81.4	01.9.16	Lu 21	1024	4 0 .	8.0	NIT		-	-		-	-
1045	aV1	o Genta	The Long	10.0	-	aVhos	an Vic	ation	Seta	Щ.e.	-	Dans,					
1.010	1.00			1915	p	CO.P.L.	1		2	14		- 1		92.22		2.41	_
Ena	Like-	100	atter a		34	mp.	88	1+11	èn,	63		20		100	3.13	÷.	
	and a	inter 1	unity 1	and i		direct of				-		1.11			- 17	111	•
0.78	-	1000	20025	-	1	10.00		100	100	100	10	10	20	100	110	PP	h
178	12	222	1.4	2	1.22	100 10	1.00	-	in	-	an	110	-	nn	00	-	11
D4II	1	22	2 72	98	1.22	- this	1 00	iiii	-0.0	Dei	00	nu	20	au	20	- 20	1.1
intz -	8	10.2	20	-81	0	04 01	00	100	80	36	00	DD.	100	00	DO.	- 66	11
0.62	i di	26	32	10	n.	100		10	82	40	100	Bd	62	20	10	80	
015	22	255	65535	8	12	88.01			22			itte	-		-	**	Ы
044	οđ.	hints:	10	16	0.	#0 0	00 1	100	00	100	an	00	05	00	00	00	
041	i al		0.00	٥î	0	15 44	1.24	- 62	64	16.8	ER.	144	64	- 64	162	44.	П
044	êΠ.	5 10		油	m	20.44	024	64	164	140	64	64	44	24	144	54	ΕI
047	10	T	5 B	10	11-	11.6	6.88	64	64	54	160	64	64	5h	Sec	(in)	
0411	- al	1	· 20	n	D:	23 0	1 00	an	00	00	an	nn.	00	00	DĎ	00	
1416	11	152		38	1	203/01	1 40	1111	00	100	-00	1112	:00	00	111	200	EI
030	11	255	65535	1	1	05.01	. 22	77		22	11	77	77	22	100	27	L
051	0	10.225	20	11	0	-04 H	00.0	00	00	00	00	00	00	00	00	005	٠

Cell capture display (hexadecimal)

NUTS 15TML 2117	3 Qu5	#Froid	di sena te	60
	v Þ	B 100-	19	Traffing Th
a series and the series of the	SLOT 9 INC	1 20826A G+8 U	NIT	
and a fragments of the second second	en la Vinéo	YCapture Setup VCa	Part Trend L	
Enable Tartie	Jump	C HEE C	AUCES C Trais	alaite .
in any yes we an	TTAR HIRT	CH3	1 interest	•
31 0 1 19 0	0 #1	+		
32 F 255 43325 T	2,48	法		
33 8 2 18 8	0.001	(†		
36 G 16 32 R	0 65	- 18 H		
15 F 255 93335 7	1.02	12		
30 0 1 19 0	10. 22	1		
38 0 2 20 0	0.04	1		
38 # 25543335 7	1.08	ī		
+0 0 2 10 0	10 011	1		
61 0 36 22 D	0.67	2		
82 D Z 14 H	0.03			
43 F 255 65535 T	1 03	14		120
,95 B 2 10 H	10.00			

Cell capture display (cell interval)

In addition to alarms and errors, any one of the delay time/2-point CDV, cell interval, or 1-point CDV can be selected and measured. The measurement results are displayed as easy-to-read bar graphs.

File Westers View Hele	MP12286 AT	d Guidley Analyzar	£.		Ġľ.
Mannane I ISTMI 21	TIME I	4Prote	1	00	21
	v >	B Contra	19	finited Th	
	SLOT 9 INC	120826A GeS UN	 Contraction 		
Constant Jump	Delay Ottaet0	Accumulate		9	
105-00	LI.	0	10	•	
			/Game With	101	
tt#iat			C. Darbert	C.Last	
			Mar	13, 814, 544	
1.087-407			Print I	13,128,124	
			Tolat	1,168,112	
19507			14-Payor	120.14	
0	1			TI dilla beel	1

Measurement results as bar graph

Up to 1023 received channels can be measured simultaneously and the traffic on the entire network can be determined by displaying and real-time monitoring of the flow of cells on each channel.

			MP12286-6	TM Goally J	Malyzer			
file .	Window	Apres Helk	the second second	- 14 - A+	and the second			
Mainh	mme 112	STMI CETI	1 310n5	#Pipid		Contraction of		1010
nici	a mi	almia		-	and the second se	all	Linter	1000
								n
-			81.07 3 3	U120828A	Gell UNIT			
Cant	autice VTa-6	stap Floor Harata	1					
Carta a						100		-
	ALL 14	a merator				10		1122
						1041	Calls	
TE.	1001	Intel	*1.1*1	ULP-1	VE-BAN	10	live	1.
U.	8	2.608+03	9.602+05	0.052400	D.01012+011	60.0	1000	
1	17	3.642+04	3.84±+04	0,00#+00	0.003+00			
				0 DDRADD	0.008+00			
- 1	10	7,688+0+	7,888+08	01008400				
1	19	7,688+04 1.158+03	7.688+04 1.152+05	0.008+00	0.008+00			
1 1 1	19	7,688+04 1.158+05 1.548+05	7.688+04 1.1180+05 1.548+05	0.008+00	0.008+00 0.008+00			
1 1 1 2	10 19 10 17	7,688+04 1.158+05 1.548+05 4.228+05	1.1580+05 1.560+05 1.300+05	0.008+00 0.008+00 1.928+05	D.008+00 0.008+00 D.008+00			
1 1 2 3 3	19 19 10 17 18	7,688+04 1.158+05 1.548+05 4.228+05 2.698+05	7.608+04 1.112+05 1.542+05 2.308+05 2.692+05	0.005+00 0.005+00 1.926+05 0.005+00	D.008+00 0.008+00 D.008+00 D.008+00			
4 4 2 2 2 2	10 19 10 17 18 19	7,688+04 1,158+03 1,548+03 4,228+03 2,698+03 3,078+03	7.608+04 1.112+05 1.542+05 2.108+05 2.692+05 3.072+05	0.008+00 0.008+00 1.928+05 0.008+00 0.008+00	D.008+00 D.008+00 D.008+00 D.008+00 D.008+80			
4 2 2 2	10 19 10 17 18 19 20	7,688+04 1.158+03 4.518+03 2.698+03 9.078+03 9.078+03	7.688+04 1.112+05 1.548+05 2.308+05 2.692+05 3.078+05 3.462+05	0.002+00 0.002+00 1.928+05 0.002+00 0.002+00 0.002+00	D.000+00 D.000+00 D.000+00 D.000+00 D.000+00 D.000+00			
1 1 2 2 2 14	19 19 17 18 19 20 32	7,688+04 1.158+03 4.258+03 2.698+03 9.078+03 3.468+03 3.848+03	7.688+04 1.112+05 1.548+05 2.308+05 2.692+05 3.078+05 3.462+05 2.642+05	0.005+00 0.005+00 1.925+05 0.005+00 0.005+00 0.505+00 0.005+00	D.000+00 D.000+00 D.000+00 D.000+00 D.000+00 D.000+00 1.330+02		ALE	

Simultaneous measurement and display of 1023 channels

Protocol Unit

This unit is used to measure different types of AAL errors.

		S linter
SLOT 4 M	U120121A PROTOCOL UNIT	
ALE (Count)	AAL5 (Count)	arrant C tars
FO Duetto+	FIFO Overfam	0
SATIFOU RIADO	SARPOLI	62 600
PC8400 4340	CPCS-FDU	6140
Firme sud	Term out	0.00
engti Enor	Leightmit	0.0
Nerve Skiel Erver 👘 🖉	Finne Skie Evor	
PtEnn n 🖓	CPIEnur	6.0
34C6mar 624 🥥	CPICEme	624. 9
e u boot	Abolt	0.0

AAL-type measurement items

8 MB of memory is allocated to Send, Receive, and Send/Receive. When the entire memory is used to receive, more than 130,000 cells can be saved at one time. The saved cells are displayed together with the time stamp. In addition, it is possible to display the cells in the specified AAL type frame format.

MP12296 ATM Gualie	Analyzar
File Wintes Yes Help	1771 - 1771 - 1771 - 1771 - 1771 - 1771 - 1771 - 1771 - 1771 - 1771 - 1771 - 1771 - 1771 - 1771 - 1771 - 1771 -
Manhane ISTMI 2111 2005 4Pint	A 010 2
	15 9 B
SLOT 4 MU12021A P	ROTOCOL UNIT
The second state of the second s	And Description
The second process (reason and a second disease of the	Tree sails
Color - 1 State - France - 4 Later	NR/ 88/29 15-31-19
Bu line o comular erestras	
Anarabakis Concisco Sinetty August	Last: Wedi
CECS-DIPO. CERVE Sample-Line CEC-DOITIONS.	
CFC3-Fej Load	A REPORT OF THE
2 61 22 22 24 24 25 20 27 28 27 48 28 48 42 1	N. 18. 17. 44
-10 11 12 12 14 14 15 10 17 10 19 18 18 11 1	L 18 17 18
10 54 10 11 56 10 10 17 16 17 24 10 11 1	10.14.19.10. ("W/sa11)*4,00
40 31 30 33 30 38 30 30 37 38 39 38 38 32 3	10.48.38 30 J22608T80.149400
44 41 42 12 49 48 48 47 18 17 45 18 45 45 45 1	ID 48 AP DD ARCORTHELIDICARDS
10 23 10 10 10 10 10 10 17 10 10 AL 10 17	TO SA IN SU SUISTANADAXIJI.
10 41 40 J3 84 85 86 J7 60 41 84 88 42 1	2 HE HF TO advertation photo havene
333 73 70 70 70 70 70 70 70 70 70 70 70 70	to 78 29 70 merupanyailin p
118 ALL DE THE AND AN AN AN AN AN AN ANY ANY AN	A MARKED AND AND A MARKED AND A MARKED
Re-1961 # OD-OL-IT.SIDEDAL	
Enserantia Coppany Timente Bassis	Seet Sted
caca-free chisa Paula-in-the cacadorarad	
the state of the last of the state of the state of the state of the	1 1 1 1 1 1 1 1 1 1 1 1 1 1 1 1 1 1 1
1 1 1 1 1 1 1 1 1 1 1 1 1 1 1 1 1 1 1	
2019944	

Example of display with more than 130,000 cells

The AAL type can be evaluated automatically for up to a maximum of 1023 received channels and the main parameters can be measured.

-			MP12	284 ATM Or	ally Analyz	21		Ŀ
Elle .	Wiado	w Ylew	Hely		Sec. Sec.			
Mark	Lieran	and the second	COMPANY AND	1111 41	015 5:Pm	itit	1 10	1001
DE			3		Galer	1	Sale	1
4			51.015	MU120021	s paotóco	UNIT	-	
Ree	untonVI	- implies	Manata		WEIGHT ST	200221		
1		a manual	(Bernell)				[Langed]	-
-	100	•	General Contraction					
191	1022	7710	ALC: DOD	CPCS-FBD	18 Kerne	M Same	Deil Lond	•
			(Della)		(Cristel)	(Sac.in)	(Drink)	-
. 0	0	Unterowe	9.042+06	-	-	+	-	1
: 10	20	AALS	1.101+06	1.105+05	-	-		
10	21	A85,3/4	8,795405	8.798409	1.4		-	
10	32	A853/4	4-398+05	6-39E+04	-		-	
10	- 25	A85374	2,645+06	2.648+05		+	(#	
10	- 24	A853/4	1,191+05	1.122101	-	+	-	
:00	25	AALS	7.018+65	-	0.005+00	0.006+00	10.008+00	
20	28	AMLS	1.512+05		0.018+00	0.006400	0.008400	
11	20	AALS	8+798+05	8.792105	+	+	. +	
11	-20	AALS	8.791+05	8.79E+04	()÷)	÷+:		1
								- Pt.

Automatic evaluation and measurement of AAL type for 1023 channels

Specifications

MP1220A ATM Quality Analyzer

Display	10.4" TFT color LCD with touch panel (analog resistive membrane)					
Memory storage	3.5" Floppy disk drive (1.44 MB/720 KB) and hard disk drive (≥500 MB)					
Buzzer	Alarm, error					
	RS-232C (D-sub 9-pin), printer (Centronics, D-sub, 25-pin), keyboard (PS/2, mini-DIN, 6-pin),					
External interface	mouse (PS/2, mini-DIN, 6-pin), VGA (analog RGB, D-sub, 15-pin)					
Slots	6 (two channels max.)					
ENC	EN55011:1991, Group 1, Class A					
EMC	Harmonic Current Emissions EN61000-3-2:1995 Class D					
Safety	EN61010-1:1993 (Installation Category II, Pollution Degree II)					
Dimensions and mass	284 (W) X 221.5 (H) X 365 (D) mm, ≤12 kg (excluding units)					
Power supply	100 to 120/200 to 240 Vac (autoswitching), 50 to 60 Hz, ≤300 VA					
Operating range	Operating: 5° to 50°C (excluding FDD), Storage: –20° to 60°C					

• MU120001A STM-4/OC-12 Unit

Bit rate	51.84, 155.52, 622.08 Mbit/s
Frames	SDH/SONET
Output signal	Connector: FC (replaceable), 1.31 µm band (SM) Clock: Internal (±10 ppm), external, receive Level (fixed value): –15 to –8 dBm Code: NRZ Optical safety: IEC825-1 Class 1, 21CFR1040.10 Class I
Input signal	Connector: FC (replaceable), 1.31 µm band (SM) Frequency range: ±100 ppm Level: -34 to -8 dBm (51.84 Mbit/s, 155.52 Mbit/s), -28 to -8 dBm (622.08 Mbit/s) Code: NRZ
Functions	SOH/POH setting, SOH/POH monitoring, path trace, empty cell setting, cell scramble (de-scramble) on/off, coset on/off, HEC error correction on/off Error addition: Bit, B1, B2, B3, FEBE-L, FEBE-P, cell Alarm addition: LOS, LOF, AIS-L, RDI-L, AIS-P, RDI-P, LCD Error measurement: B1, B2, B3, MS-REI (FEBE-L), HP-REI (FEBE-P), HEC corrected cells, HEC uncorrected cells Alarm measurement: LOS, OOF, LOF, MS-AIS (AIS-L), MS-RDI (RDI-L), AU-AIS (AIS-P), HP-RDI (RDI-P), AU-LOP (LOP-P), LCD Pointers: Monitor, ±justification, NDF Auxiliary output: Receive clock output, trigger output

• MU120002A STM-1/OC-3 Unit

Bit rate	155.52 Mbit/s
Frames	SDH/SONET
Output signal	Connector Optical: SC 1.31 μm (SM), Electrical: BNC 75 Ω Clock: Internal (±10 ppm), external, receive Optical level (fixed value): -15 to -8 dBm Electrical level: 1 ±0.1 Vp-p (CMI) Code Optiacal: NRZ, Electrical: CMI Optical safety: IEC825-1 Class 1, 21CFR1040.10 Class I
Input signal	Connector Optical: SC 1.31 μm (SM/MM), Electrical: BNC 75 Ω Frequency range: ±100 ppm Optical level: -28 to -8 dBm (SM) Electrical level: 1±0.1 Vp-p (CMI)*, Cable loss: 0 to 12 dB, Monitor: 20 dB attenuated level of above level can be applied. Code Optical: NRZ, Electrical: CMI
Functions	SOH/POH setting, SOH/POH monitoring, path trace, empty cell setting, cell scramble (de-scramble) on/off, coset on/off, HEC error correction on/off Error addition: Bit, B1, B2, B3, FEBE-L, FEBE-P, cell Alarm addition: LOS, LOF, AIS-L, RDI-L, AIS-P, RDI-P, LOP-P, LCD Error measurement: B1, B2, B3, MS-REI (FEBE-L), HP-REI (FEBE-P), HEC corrected cells, HEC uncorrected cells Alarm measurement: LOS, OOF, LOF, MS-AIS (AIS-L), MS-RDI (RDI-L), AU-AIS (AIS-P), HP-RDI (RDI-P), AU-LOP (LOP-P), LCD Pointers: Monitor, ±justification, NDF, history record Auxiliary output: Receive clock output, trigger output

• MU120010A T1/T3 Unit

Bit rate	1.544 Mbit/s (T1), 44.736 Mbit/s (T3)
Frames	1.5M ESF (PLCP: on/off), 45M C-bit parity (PLCP: on/off), 45M M23 (PLCP: on/off)
Output signal	Connector BNC: 75 Ω unbalanced (T3) 8-pin modular: 100 Ω balanced (ISO/IEC 10173, T1) Clock: Internal (±10 ppm), external, receive Level: 2.4 to 3.6 Vo-p (T1), 0.36 to 0.85 Vo-p (T3) Code T1: B8ZS, T3: B3ZS
Input signal	Connector BNC: 75 Ω unbalanced (T3) 8-pin modular: 100 Ω balanced (ISO/IEC 10173, T1) Frequency range: ±130 ppm (T1), ±20 ppm (T3) Level: 2.4 to 3.6 Vo-p (T1), 0.36 to 0.85 Vo-p (T3) Monitor: 20 dB attenuated level of above level can be applied. Code T1: B8ZS, T3: B3ZS
Functions	Empty cell setting, cell scramble (de-scramble) on/off, coset on/off, HEC error correction on/off Error addition: Bit, FEBE, PLCP-BIP-8, PLCP-FEBE, cell Alarm addition: LOF, LOS, AIS, yellow, idle, PLCP-LOF, PLCP-yellow, LCD Error measurement: Code, CP, FEBE, CRC6, PLCP-BIP-8, PLCP-FEBE, HEC corrected cells, HEC uncorrected cells Alarm measurement: LOS, OOF, AIS, yellow, idle, PLCP-OOF, PLCP-yellow, LCD Auxiliary output: Receive clock output, trigger output

• MU120011A E1/E3/E4 Unit

Bit rate	2.048 Mbit/s (E1), 34.368 Mbit/s (E3), 139.264 Mbit/s (E4)
Frames	2M-CRC-4 off (PLCP: on/off), 2M CRC4 on (PLCP: on/off), 34M G.751 (PLCP: on), 34M GH.832 (PLCP: off), 139M G.832 (PLCP: off)
Output signal	Connector D-sub (9-pin): 120 Ω balanced (E1), BNC: 75 Ω unbalanced (E1/E3/E4) Clock: Internal (±10 ppm), external, receive Level: 3 ±0.3 Vo-p (E1 balanced), 2.37 ±0.237 Vo-p (E1 unbalanced), 1 ±0.1 Vo-p (E3), 1 ±0.1 Vp-p (E4) Code E1/E3: HDB3, E4: CMI
Input signal	Connector D-sub (9-pin): 120 Ω balanced (E1), BNC: 75 Ω unbalanced (E1/E3/E4) Frequency range: ±100 ppm (E1/E4), ±20 ppm (E3) Level: 3 ±0.3 Vo-p (E1 balanced), 2.37 ±0.237 Vo-p (E1 unbalanced), 1 ±0.1 Vo-p (E3), 1 ±0.1 Vp-p (E4) *Cable loss: 0 to 6 dB (E1), 0 to 12 dB (E3, E4) Monitor: 20 dB attenuated level of above level can be applied. Code E1/E3: HDB3, E4: CMI
Functions	Empty cell setting, cell scramble (de-scramble) on/off, coset on/off, HEC error correction on/off (E1, E3) Error addition: Bit, BIP-8, REI, PLCP-BIP-8, PLCP-FEBE, cell Alarm addition: LOF, LOS, AIS, RA, RA (MF), RDI, PLCP-LOF, PLCP-yellow, LCD Error measurement: CRC4, code, BIP-8, REI, PLCP-BIP-8, PLCP-FEBE, HEC corrected cells, HEC uncorrected cells Alarm measurement: LOS, OOF, AIS, MF loss (CRC), MF loss (sig), RA, RA (MF), RDI, PLCP-OOF, PLCP-yellow, LCD Trail trace: Monitor, setting Auxiliary output: Receive clock output, trigger output

• MU120012A E1/E3 Unit

Bit rate	2.048 Mbit/s (E1), 34.368 Mbit/s (E3)
Frames	2M-CRC-4 off (PLCP: on/off), 2M CRC4 on (PLCP: on/off), 34M G.751 (PLCP: on), 34M G.832 (PLCP: off)
Output signal	Connector D-sub (9-pin): 120 Ω balanced (E1), BNC: 75 Ω unbalanced (E1/E3) Clock: Internal (±10 ppm), external, receive Level: 3 ±0.3 Vo-p (E1 balanced), 2.37 ±0.237 Vo-p (E1 unbalanced), 1 ±0.1 Vo-p (E3) Code: HDB3
Input signal	Connector D-sub (9-pin): 120 Ω balanced (E1), BNC: 75 Ω unbalanced (E1/E3) Frequency range: ±100 ppm (E1), ±20 ppm (E3) Level: 3 ±0.3 Vo-p (E1 balanced), 2.37 ±0.237 Vo-p (E1 unbalanced), 1 ±0.1 Vo-p (E3) *Cable loss: 0 to 6 dB (E1), 0 to 12 dB (E3) Monitor: 20 dB attenuated level of above level can be applied. Code: HDB3
Functions	Empty cell setting, cell scramble (de-scramble) on/off, coset on/off, HEC error correction on/off Error addition: Bit, BIP-8, REI, PLCP-BIP-8, PLCP-FEBE, cell Alarm addition: LOF, LOS, AIS, RA, RA (MF), RDI, PLCP-LOF, PLCP-yellow, LCD Error measurement: CRC4, code, BIP-8, REI, PLCP-BIP-8, PLCP-FEBE, HEC corrected cells, HEC uncorrected cells Alarm measurement: LOS, OOF, AIS, MF Loss (CRC), MF Loss (Sig), RA, RA (MF), RDI, PLCP-OOF, PLCP-yellow, LCD Trail trace: Monitor, setting Auxiliary output: Receive clock output, trigger output

• MU120015A ATM 25M Unit

Bit rate	32.00 Mbit/s (25M)
Output signal	Connector: 8-pin modular jack, 100 Ω (RJ45) Clock: Internal (±10 ppm), external, receive Level: 2.7 to 3.4 Vp-p (1 symbol) Code: NRZI (4B/5B)
Input signal	Connector: 8-pin modular jack, 100 Ω (RJ45) Frequency: ±100 ppm Level: 2.7 to 3.4 Vp-p (1 symbol) Code: NRZI (4B/5B)
Functions	Empty cell setting, coset on/off Error addition: Code, cell Alarm addition: LOS Error measurement: Code, HEC uncorrected cell, illegal cell Alarm measurement: LOS Sync event: Send, measure Auxiliary output: Receive clock output, trigger output

• MU120016A 6.3M Unit

Bit rate	6.312 Mbit/s (6.3M)
Output signal	Connector: BNC, 75 Ω Clock: Internal (±10 ppm), external, receive Level: 2 ±0.3 Vo-p Code: B8ZS
Input signal	Connector: BNC, 75 Ω Frequency: ±30 ppm Level: 2 ±0.3 Vo-p *Cable loss: 0 to 6 dB Monitor: 20 dB attenuated level of above level can be applied. Code: B8ZS
Functions	Empty cell setting, cell scramble (de-scramble) on/off, coset on/off, HEC error correction on/off Error addition: Bit, CRC5, cell Alarm addition: LOS, AIS, RAI, LOF, LCD Error measurement: CRC5, HEC corrected cell, HEC uncorrected cell Alarm measurement: LOS, AIS, RAI, LOF, LCD Auxiliary output: Receive clock output, trigger output

• MU120017A 6.3/25M Unit

Bit Rate	6.312 Mbit/s (6.3M), 32.00 Mbit/s (25M)
Output signal	Connector BNC: 75 Ω (6.3M), 8-pin modular jack, 100 Ω (RJ45, 25M) Clock: Internal (±10 ppm), external, receive Level: 2 ±0.3 Vo-p (6.3M), 2.7 to 3.4 Vp-p (25M, 1 symbol) Code 6.3M: B8ZS, 25M: NRZI (4B/5B)
Input signal	Connector BNC: 75 Ω (6.3M), 8-pin modular jack, 100 Ω (RJ45, 25M) Frequency range: ±30 ppm (6.3M), ±100 ppm (25M) Level: 2 ±0.3 Vo-p (6.3M), 2.7 to 3.4 Vp-p (25M, 1 symbol) *Cable loss: 0 to 6 dB (6.3M) Monitor: 20 dB attenuated level of above level can bo applied (6.3M). Code 6.3M: B8ZS, 25M: NRZI (4B/5B)
Functions	Empty cell setting, cell scramble (de-scramble) on/off (6.3M only), coset on/off, HEC error correction on/off (6.3M only), sync event send (25M only) Error addition 6.3M: Bit, CRC5, cell 25M: Code, cell Alarm addition 6.3M: LOS, AIS, RAI, LOF, LCD 25M: LOS Error measurement 6.3M: CRC5, HEC corrected cell, HEC uncorrected cell 25M: Code, HEC uncorrected cell, illegal cell Alarm measurement 6.3M: LOS, AIS, RAI, LOF, LCD 25M: LOS Sync event (25M only): Send, measure Auxiliary output: Receive clock output, trigger output

MU120020A QoS Unit

Foreground cells (test cells)	O.191, extended O.191, OAM test cell (PRBS 15), null, AAL1, AAL3/4, (For null, AAL1, AAL3/4, next pattern settable to payload. PRBS 9, PRBS 15, PRBS 15 (non-inverted), PRBS 23, time stamp, programmable)
Cell generation timing	CBR, burst, sawtooth waveform, CBR with CDV, Poisson distribution, manual, external edge, external level, detailed CBR, burst for UPC measurement, programmable
Background cell	CBR (10 types)
OAM cell	AIS, RDI, continuity check, loopback, programmable, forward monitoring, backward reporting, PM activation/deactiva- tion, CC activation/deactivation
Capture	Capacity: 4095 cells Filter: All cells, specified cells, header + first byte of payload match/mismatch cells Trigger: Manual, OAM cell receive, cell error detect, cell loss detect, cell misinsertion detect, cell tagging, external input signal, etc. Display: Hexadecimal, ASCII, cell interval, translate
Single-channel	 Error addition: Cell loss, cell error Error detection: Bit error, error cell, cell loss, cell misinsertion, non-conforming cell, etc. (measurement items differ according to test cell) Alarm detection: VP-AIS, VP-RDI, VP-LOC, VC-AIS, VC-RDI, VC-LOC Others: Bandwidth, total cells, cell delay measurement, 1 point CDV measurement, 2 point CDV measurement, cell interval measurement
1023 channel measurement (live monitor)	Detect and measure 1023 channels on line Measurement items: Total cell count, CLP=0 cell count, CLP=1 cell count, OAM cell count
Auxiliary input	Trigger input

MU120021A Protocol Unit

Send/receive memory	8 MB (≥130,000 cells, send: 8 MB, receive: 8 MB, send + receive: 4 + 4 MB selectable)
Cell send	Transmit from memory according to time stamp. Able to transmit in every 1 cell Able to edit AAL1, AAL3/4, AAL5 frame
Capture	Capacity: ≥130,000 cells (at 8 MB receive setting) Filter: All cells, all cells (excluding idle cells), up to 16 specified channels Trigger: Specified event, specified event occurrence times, sequential event (second event after first event) Event: Specified channel, SN abnormality, ST abnormality, CRC abnormality, specified pattern, external input signal, etc. Display: Cell, SAR, CPCS, time stamp
Single-channel measurement	AAL type automatic evaluation and measurement Error addition: Cell loss, cell error Measurement items: Cell count, CPCS-PDU count, assembled timer timeout PDU count, frame size error count, CPI error count, SN error count, ST error count, LI error count, about count, BE tag error count, BA size error count, AL error count, length error count, CRC error count, etc. (measurement items differ according to AAL type)
1023 channel measurement (live monitor)	Detect and measure 1023 channels on line. AAL type automatically detected and measured Measurement items: Cell count, CPCS count, etc. (measurement items differ according to AAL type)
External interface	Trigger input (capture event)

Ordering Information

Please specify model/order number, name and quantity when ordering.

Model/Order No.	Name
MB1220A	Main unit
WIP 1220A	MP1220A ATM Quality Analyzer
F0012 W1304AE W1305AE Z0339 Z0340B Z0343A Z0343A Z0345A	AccessoriesAC power cord:1 pcFuse, 3.15 A:2 pcsMP1220A operation manual:1 copyMP1220A remote control operation manual:1 copySoftware recovery floppy disk*:1 pcProtective cover (without keyboard):1 pcInput pen:1 pcAccessory bag:1 pc
MP1220A-01 MP1220A-02 MP1220A-03 MU120001A-38 MU120001A-39 MU120001A-40 MU120001A-43	Options RS-232C control GPIB control Ethernet control ST connector DIN connector SC connector HMS-10/A connector
MU120001A	STM-4/OC-12 Unit
W1308AE	MU120001A operation manual
W1314AE	MU120001A remote control operation manual
MU120002A	STM-1/OC-3 Unit
W1309AE	MU120002A operation manual
W1315AE	MU120002A remote control operation manual
MU120010A	T1/T3 Unit
W1310AE	MU120010A operation manual
W1316AE	MU120010A remote control operation manual
MU120011A	E1/E3/E4 Unit
W1311AE	MU120011A/120012A operation manual
W1317AE	MU120011A/120012A remote control operation manual
MU120012A	E1/E3 Unit
W1311AE	MU120011A/120012A operation manual
W1317AE	MU120011A/120012A remote control operation manual
MU120015A	ATM25M Unit
W1312AE	MU120015A/120016A/120017A operation manual
W1318AE	MU120015A/120016A/120017A remote control operation manual
MU120016A	6.3M Unit
W1312AE	MU120015A/120016A/120017A operation manual
W1318AE	MU120015A/120016A/120017A remote control operation manual
MU120017A	6.3/25M Unit
W1312AE	MU120015A/120016A/120017A operation manual
W1318AE	MU120015A/120016A/120017A remote control operation manual
MU120020A	QoS Unit
W1313AE	MU120020A operation manual
W1319AE	MU120020A remote control operation manual
MU120021A	Protocol Unit
W1371AE	MU120021A operation manual
W1372AE	MU120021A remote control operation manual
MX122020A	Protocol Decoding Software
W1648AE	MX122020A operation manual
J0008 J0775D J0635B J0660B J0796A J0796B J0796C J0796D J0796E J0844A J0838A Z0319A Z0340A Z0340B B0414A	Optional accessories GPIB cable, 2 m Coaxial cord, 2 m (75 Ω) BNC cord, 2 m (twin shield) Optical fiber cord (FC/PC-FC/PC-2m-SM), 2 m Optical fiber cord (SC/PC-SC/PC-2m-SM), 2 m Replaceable optical connector (ST) Replaceable optical connector (SC) Replaceable optical connector (SC) Replaceable optical connector (FC) ISO 10173 cable (T1), 2 m UTP category 3 cable (25M), 2 m Ps/2 mouse Protective cover (with keyboard) Protective cover (without keyboard) Hard case Soft acco
*Sold only to MP1220A	ISERS

15



ANRITSU CORPORATION

MEASUREMENT SOLUTIONS 5-10-27, Minamiazabu, Minato-ku, Tokyo 106-8570, Japan Phone: +81-3-3446-1111 Telex: J34372 Fax: +81-3-3442-0235

• U.S.A. ANRITSU COMPANY North American Region Headquarters

1155 East Collins Blvd., Richardson, Tx 75081, U.S.A. Toll Free: 1-800-ANRITSU (267-4878) Phone: +1-972-644-1777 Fax: +1-972-671-1877

Canada

ANRITSU ELECTRONICS LTD.

Unit 102, 215 Stafford Road West Nepean, Ontario K2H 9C1, Canada Phone: +1-613-828-4090 Fax: +1-613-828-5400

Brasil

ANRITSU ELETRÔNICA LTDA. Praia de Botafogo 440, Sala 2401 CEP 22250-040, Rio de Janeiro, RJ, Brasil Phone: +55-21-5276922 Fax: +55-21-537-1456

• U.K.

ANRITSU LTD.

200 Capability Green, Luton, Bedfordshire LU1 3LU, U.K. Phone: +44-1582-433200 Fax: +44-1582-731303

• Germany ANRITSU GmbH

Grafenberger Allee 54-56, 40237 Düsseldorf, Germany Phone: +49-211-96855-0 Fax: +49-211-96855-55

France ANRITSU S.A.

9, Avenue du Québec Z.A. de Courtabœuf 91951 Les Ulis Cedex, France Phone: +33-1-60-92-15-50 Fax: +33-1-64-46-10-65

Italy

ANRITSU S.p.A. Via Elio Vittorini, 129, 00144 Roma EUR, Italy Phone: +39-06-509-9711 Fax: +39-06-502-24-25

Sweden ANRITSU AB

Botvid Center, Fittja Backe 1-3 145 84 Stockholm, Sweden Phone: +46-853470700 Fax: +46-853470730

• Spain

ANRITSU ELECTRÓNICA, S.A. Europa Empresarial Edificio Londres, Planta 1, Oficina 6 C/ Playa de Liencres, 2 28230 Las Rozas. Madrid, Spain Phone: +34-91-6404460 Fax: +34-91-6404461

Specifications are subject to change without notice.

• Singapore

ANRITSU PTE LTD. 6, New Industrial Rd., #06-01/02, Hoe Huat Industrial Building, Singapore 536199 Phone: +65-282-2400 Fax: +65-282-2533

Hong Kong

ANRITSU COMPANY LTD. Suite 719, 7/F., Chinachem Golden Plaza, 77 Mody Road, Tsimshatsui East, Kowloon, Hong Kong, China

Phone: +852-2301-4980 Fax: +852-2301-3545

Korea ANRITSU CORPORATION

14F Hyun Juk Bldg. 832-41, Yeoksam-dong, Kangnam-ku, Seoul, Korea Phone: +82-2-553-6603 Fax: +82-2-553-6604~5

Australia ANRITSU PTY LTD.

Unit 3/170 Forster Road Mt. Waverley, Victoria, 3149, Australia Phone: +61-3-9558-8177 Fax: +61-3-9558-8255 Taiwan

ANRITSU COMPANY INC.

6F, 96, Sec. 3, Chien Kou North Rd. Taipei, Taiwan Phone: +886-2-2515-6050 Fax: +886-2-2509-5519