

# AMP100

## Mini-size Amplifier



# User's Manual

Thank you for purchasing the Mini Amplifier AMP100 Series of ARRAY ELECTRONIC CO., LTD. To use this product better, you are recommended to take some time to read this manual.

AMP100 Series Mini Amplifier is a waist banded mini amplifier, suitable for small meeting, party, teaching, touring travel and so on activities

## NOTES:

1. The AC/DC transformer cannot be used as recharger. When using the transformer, please take out the batteries.
2. No time no using, please take out the batteries.
3. When the indicator of the batteries is flashing or the sound becomes lower, please change the batteries in time.

## Function Features:

- Light and handy design, carrying freely and smoothly
- Using four units of ordinary or rechargeable batteries “AA” . With enough capacity, the batteries can be used for a long time.
- Built-in speaker of large power to ensure the tone of the output be better.
- Equipped waistbelt makes it more flexible and convenient for carry.

## Technical Specification:

<b>Power Supply</b>	<b>4 X 1.5VAA Alkaline</b>
	<b>Input Power: DC 6-9V 1A</b>
<b>Output Power</b>	<b>2W</b>
<b>Directivity</b>	<b>Unidirectional</b>
<b>Weight</b>	<b>245g (Excluding the batteries)</b>
<b>Dimensions</b>	<b>124 X 76 X 50 (mm)</b>

## Selectable Accessories:





Headset Microphone  
(HM01)



Switching Power  
(SP0910A)



Waist Belt  
(WB01)



Notes: When installing the batteries, pay attention to the polarity of the batteries. Suitably adjust the rotary of the volume to reach the better result.

Ver: 1.0



**ARRAY**

**ARRAY ELECTRONIC CO., LTD.**

XISHANQIAO YUHUATAI ZONE, NANJING, 210041, CHINA

TEL: +86-25-5280 1556 EXT 223

FAX: +86-25-5280 1218

DIRECTLINE: +86-25-5280 2814

EMAIL: [jennifer@array.sh](mailto:jennifer@array.sh)

<http://www.array.sh>