

Manual Supplement

Manual Title: 725 Users
Print Date: October 1998
Revision/Date: 3, 5/04

Supplement Issue: 1
Issue Date: 12/04
Page Count: 1

This supplement contains information necessary to ensure the accuracy of the above manual. This manual is distributed as an electronic manual on the following CD-ROM:

CD Title:	725 Product Manuals
CD Rev. & Date:	3, 5/2004
CD PN:	1549615

Change #1

On page 59, under *RTD Excitation (simulation)* change the following:

From:

PT 200-385	0.15 to 3.0 ma
------------	----------------

To:

PT 200-385	0.05 to 0.80 ma
------------	-----------------

Under *Temperature, RT Ranges, and Accuracies (ITS-90)* replace the **Allowable excitation current (source)** with the following:

Ni120, Pt100-385, Pt100-392, Pt100-JIS: 0.15 to 3.0 mA

Pt200-385, Pt500-385: 0.05 to 0.80 mA; Pt1000-385: 0.05 to 0.40 mA