

Supported Printers

1-Dec-04

| | | | G=PIIB U=USB P=Parallel Interface | 4294A P | 4395A 4396B P | E5100A P | E4991A P / U | E5070B E5071B P / U | E5061A E5062A P / U | E5052A P / U | |
|--------------|--------------------|---------|--------------------------------------------|------------|---------------------|-------------|-----------------|---------------------------|---------------------------|-----------------|-----------|
| HP | New New | 6840 | U | - | - | - | YES(8)(9) | YES(4)(6)(8)(10) | YES(4)(8)(9) | YES(4)(8)(9) | |
| | | 5740 | U | - | - | - | YES(8)(9) | YES(4)(6)(8)(10) | YES(4)(8)(9) | YES(4)(8)(9) | |
| | | | 5650 | P / U | Yes(3) | Yes(3) | Yes | Yes(7)(11) | Yes(3)(11) | YES(4)(9) | Yes(4)(9) |
| | | | 1200C | P | Yes | Yes | Yes(1) | - | - | - | - |
| | | | 3820 | P / U | Yes | Yes(3) | Yes(1)(5) | Yes(7)(11) | Yes(11) | - | - |
| | | | 5550 | P / U | Yes | Yes(3) | Yes(1)(5) | Yes(7)(11) | Yes(11) | - | - |
| | | | 672C | P | Yes | Yes | Yes (1) | - | - | - | - |
| | | | 690C | P | Yes | Yes | - | - | - | - | - |
| | | | 694C | P | Yes | Yes | Yes (1) | - | - | - | - |
| | | | 850C | P | Yes | Yes | - | - | - | - | - |
| | | | 870C | P | Yes | Yes | - | - | - | - | - |
| | | | 880C | P | Yes | Yes | Yes(1)(5) | - | - | - | - |
| | | | 895Cxi | P | Yes | Yes | Yes(1)(5) | Yes(7)(11) | - | - | - |
| | | | 930C | P / U | Yes | Yes(3) | Yes(1)(5) | Yes(7)(11) | - | - | - |
| | | 940C | P / U | Yes | Yes(3) | Yes(1)(5) | Yes(7)(11) | - | - | - | |
| | | 948C | P / U | Yes | Yes(3) | Yes(1)(5) | Yes(7)(11) | - | - | - | |
| | | 970Cxi | P | Yes | Yes(3) | Yes (1) | Yes(7)(11) | - | - | - | |
| EPSON | | PM720C | P | - | - | - | Yes(7)(16) | - | - | - | |
| CANON | | BJ F210 | P | - | - | - | Yes(7)(17) | - | - | - | |

- (1) - Works in black and white mode only.
- (2) - For Instruments not equipped with a parallel interface, the GPIB to parallel converter (Micro Print 45CH) of Intelligent Interfaces Inc. is REQUIRED to operate printers with a parallel interface. For more detail information about Micro Print 45CH, please visit Intelligent Interfaces, Inc web site at: <http://www.intelligentinterfaces.com>
- (3) - When the power-on switch of the printer flickers, you will be able to print the screen image of instrument using the following procedure.
 - 1) Press the "COPY ABORT" key of instruments. 2) Press "Print Standard" key of instrument.
- (4) - When the power-on switch of the printer flickers, wait until it ends and the light comes on for the next print out.
- (5) - Applies only to the E5100A/B with F/W rev.3.20 or later.
- (6) - Applies only to instruments with Serial Number above JP1KK00156 or MY42100139 for E5070B, with Serial Number above JP1KK00395 or MY42100226 for E5071B.
- (7) - Works in Windows 98 OS and Parallel Port Only
- (8) - Works in Windows 2000 OS and USB Port Only
- (9) - Use HP DJ5600 Printer Driver of Windows 98/2000 operating system
- (10) - Use HP DJ5550 Printer Driver of Windows 98/2000 operating system
- (11) - Use HP DJ550C Printer Driver of Windows 98/2000 operating system
- (12) - Use HP DJ970C Printer Driver
- (13) - Use HP DJ930C Printer Driver that is installed in the E5070/71A
- (14) - Use HP DJ940C Printer Driver that is installed in the E5070/71A
- (15) - Use HP DJ948C Printer Driver that is installed in the E5070/71A
- (16) - Use EPSON Stylus Color ESC/P2 Printer Driver of Windows 98 operating system
- (17) - Use CANON BJC600 Printer Driver of Windows 98 operating system

Products with No Graphics Display (LCR Meter)

| | | | G=PIIB U=USB P=Parallel Interface | 4263B 4338B 4339B G (2) | 4349B G (2) | 4284A 4285A G (2) | 4268A No support | 4288A No support | 4279A No support | 4287A P/U(7) |
|--------------|--------------------|---------|--------------------------------------------|----------------------------------|----------------|-------------------------|---------------------|---------------------|---------------------|-----------------|
| HP | New New | 6840 | U | - | - | - | - | - | - | - |
| | | 5740 | U | - | - | - | - | - | - | - |
| | | | 5650 | P / U | - | - | - | - | - | - |
| | | | 1200C | P | Yes (1) | Yes (1) | Yes (1) | - | - | - |
| | | | 3820 | P / U | Yes (1) | - | Yes (1) | - | - | Yes(11) |
| | | | 5550 | P / U | Yes (1) | - | Yes (1) | - | - | Yes(11) |
| | | | 672C | P | Yes (1) | Yes (1) | Yes (1) | - | - | - |
| | | | 690C | P | - | - | - | - | - | - |
| | | | 694C | P | Yes (1) | Yes (1) | Yes (1) | - | - | - |
| | | | 850C | P | Yes (1) | Yes (1) | Yes (1) | - | - | - |
| | | | 870C | P | Yes (1) | Yes (1) | Yes (1) | - | - | - |
| | | | 880C | P | Yes (1) | Yes (1) | Yes (1) | - | - | - |
| | | | 895Cxi | P | Yes (1) | Yes (1) | Yes (1) | - | - | Yes(12) |
| | | | 930C | P / U | Yes (1) | - | Yes (1) | - | - | Yes(12) |
| | | 940C | P / U | Yes (1) | - | Yes (1) | - | - | Yes(12) | |
| | | 948C | P / U | Yes (1) | - | Yes (1) | - | - | Yes(12) | |
| | | 970Cxi | P | - | - | - | - | - | - | Yes(12) |
| EPSON | | PM720C | P | - | - | - | - | - | - | - |
| CANON | | BJ F210 | P | - | - | - | - | - | - | - |

Discontinued Products

| | | | G=PIIB U=USB P=Parallel Interface | 4194A G (2) | 4278A G (2) | 4286A G (2) | 4291B P | 4352B P | E5070A E5071A P (7) |
|-----------|--------------------|--------|--------------------------------------------|----------------|----------------|----------------|------------|------------|---------------------------|
| HP | New New | 6840 | U | - | - | - | - | - | - |
| | | 5740 | U | - | - | - | - | - | - |
| | | | 5650 | P / U | - | - | - | Yes(3) | Yes |
| | | | 1200C | P | Yes (1) | Yes (1) | - | Yes | Yes(11) |
| | | | 3820 | P / U | - | - | - | Yes(3) | Yes(3) |
| | | | 5550 | P / U | - | - | - | Yes(3) | Yes(3) |
| | | | 660C | P | Yes (1) | Yes(1) | - | - | Yes |
| | | | 672C | P | Yes (1) | Yes (1) | - | Yes | Yes |
| | | | 690C | P | - | - | - | Yes | Yes |
| | | | 694C | P | Yes (1) | Yes (1) | - | Yes | Yes |
| | | | 850C | P | Yes (1) | Yes (1) | - | Yes | Yes |
| | | | 870C | P | Yes (1) | Yes (1) | - | Yes | Yes |
| | | | 880C | P | Yes(1) | Yes (1) | Yes | Yes | Yes |
| | | | 895Cxi | P | Yes(1) | Yes (1) | Yes | Yes | Yes |
| | | 930C | P | Yes(1) | Yes (1) | - | Yes(3) | Yes(3) | |
| | | 940C | P / U | - | Yes (1) | - | Yes(3) | Yes(3) | |
| | | 948C | P / U | - | Yes (1) | - | Yes(3) | Yes(3) | |
| | | 970CXI | P | Yes(1) | - | Yes | Yes(3) | Yes | |