

MODIFICATION RECOMMENDED –  
CORRECTS MANUFACTURING OR DESIGN DEFECTS

**4263B-08**

# S E R V I C E N O T E

Supersedes:  
NONE

4263B LCR Meter

Serial Numbers: MY40102391 / MY40102823

**Incorrect characters might be displayed on rare occasions**

**To Be Performed By: Agilent-Qualified Personnel**

**Parts Required:**

P/N	Description	Qty.
04263-61011	LCD ASSY	1

## ADMINISTRATIVE INFORMATION

SERVICE NOTE CLASSIFICATION:			
<b>MODIFICATION RECOMMENDED</b>			
ACTION CATEGORY:	<input type="checkbox"/> IMMEDIATELY X ON SPECIFIED FAILURE <input type="checkbox"/> AGREEABLE TIME	STANDARDS: LABOR: 0.2 Hours	
LOCATION CATEGORY:	<input type="checkbox"/> CUSTOMER INSTALLABLE <input type="checkbox"/> ON-SITE X SERVICE CENTER	SERVICE INVENTORY: <input type="checkbox"/> RETURN X SCRAP <input type="checkbox"/> SEE TEXT	USED PARTS: <input type="checkbox"/> RETURN X SCRAP <input type="checkbox"/> SEE TEXT
AVAILABILITY:	PRODUCT'S SUPPORT LIFE	AGILENT RESPONSIBLE UNTIL: Sep 2006	
AUTHOR: KW      PRODUCT LINE: WN			
ADDITIONAL INFORMATION:			

© AGILENT TECHNOLOGIES, INC. 2004  
PRINTED IN U.S.A.



September 22, 2004

**Situation:**

Some of the meters specified above may have a defective LCD assembly. When the meter is turned on, incorrect characters might be displayed on rare occasions due to its LCD assembly failure. Once the incorrect characters are displayed, they remain on the screen until the meter is turned off.

The figures below show examples of the incorrect characters.

**Solution/Action:**

Replace the LCD assembly with a new one.