## INSTRUCTION MANUAL




KEPCO An ISO 9001 Company.

KIT DIN PAT-L

## DIN-RAIL MOUNTING KIT FOR SERIES PAT

**DESCRIPTION.** Kepco KIT, Models DIN PAT-L, contains two preassembled mounting clips and associated hardware used to install PAT Series power supplies on a DIN rail. The "L" suffix is for mounting along the long dimension (length) as shown in Figure 1. Outline dimensions are shown in Figure 4.



3041955

FIGURE 1. L SUFFIX ORIENTATION

**INSTALLING KIT.** Attach the preassembled mounting clips to the power supply using the hardware supplied (see Figure 3). The clips may be mounted with the release lever on either side to facilitate removal.

**INSTALLING POWER SUPPLY ON DIN RAIL.** To mount the power supply on the rail insert one end of both clamps under one edge of the rail, then snap the other end of the two clips into place (see Figure 2A).

**REMOVING POWER SUPPLY FROM DIN RAIL.** While grasping the power supply with one hand, use a screwdriver to apply leverage towards the left as shown in Figure 2B to disengage each clip from the rail. Where mounting clips are close together, it may be necessary to apply leverage with two screwdrivers simultaneously.




FIGURE 2. INSTALLATION AND REMOVAL OF POWER SUPPLY FROM DIN RAIL

KEPCO, INC. ● 131-38 SANFORD AVENUE ● FLUSHING, NY. 11352 U.S.A. ● TEL (718) 461-7000 ● FAX (718) 767-1102 http://www.kepcopower.com ● email: hq@kepcopower.com




FIGURE 3. INSTALLATION OF KIT ON PAT POWER SUPPLY

6.3811 -NOTE: DIMENSIONS ARE IN INCHES. DIMENSIONS ARE IN BRACKETS **(**P) ARE IN MILLIMETERS.  $3\frac{11}{32}$ ⊕ ⊗ 00000 00000 00000 \_\_\_ 0.983 [24.96] 1.680 3.28 [42.67] 2.224 [83.3] [56.50] 1.376 [35.00] 3041959

FIGURE 4. OUTLINE DIMENSIONS

KEPCO, INC. ● 131-38 SANFORD AVENUE ● FLUSHING, NY. 11352 U.S.A. ● TEL (718) 461-7000 ● FAX (718) 767-1102 http://www.kepcopower.com ● email: hq@kepcopower.com 228-1354