RELEASE NOTES

Product: FW for A 1378

Version: 1.1.07 - E

Release date:17.4.2013

DESCRIPTION OF THE RELEASED PRODUCT:

FW for A 1378 PV Remote Unit

DESCRIPTION OF CHANGES, DEPENDENCES AND HISTORY:

	MI 3109			UM	PC SW	Minimal FW version of related instruments	
#	FW ver.	Description of changes:	HW version	version	Appl. Name and ver.	MI 3108	MI 3109
3							
2							
1	1.1.07-E	First release	HW 1	1.1	EuroLink PRO EU:4.23 UK:5.17 DEU:7.19	2.1.95-E1	1.1.150-E1

INSTALLATION PROCEDURE:

Please follow the following instructions carefully!

- 1.) Connect a PC to the instrument with a serial cable (Supplied with the tester), either direct to computer or via a USB/serial converter.
- 2.) Unzip the attached zip file.
- 3.) Open the extracted folder and run the "FlashMe.exe" and follow instructions inside the application.*
 - Connect a PC to the instrument with the original supplied serial cable.
 - Select the COM port to which serial cable is connected to. (See Extra Notes)
 - If connected, disconnect the charger.
 - On instrument hold down UP and LIGHT keys and turn ON the instrument (or connect charger).
 - Press CONTINUE button on the PC-SW.
 - Wait until the instrument's firmware is updated.
- * If "FlashMe.exe" fails to start do the following:
 - right click on "FlashMe.exe"
 - click Properties
 - click Compatibility tab
 - click on the checkbox near the label: "Run this program in compatibility mode for:"
 - in the dropdown menu select "Windows 7" or "Windows XP" if the former doesn't work
 - click OK, and try to run "FlashMe.exe" again

EXTRA Notes:

Your computers COM port can be identified by viewing windows device manager and looking in "Ports/ Comm & LPT". If nothing is listed here you do not have a COM port or the drivers for the USB/Serial converter are not correctly installed.

COMPANY DATA:

METREL d.d. Measuring and Regulation Equipment Manufacturer

Ljubljanska 77 SI-1354 Horjul Tel: + 386 (0)1 75 58 200 Fax: + 386 (0)1 75 49 226 E-mail: metrel@metrel.si http://www.metrel.si