



STANFORD RESEARCH SYSTEMS

High voltage power supplies



The PS300 Series

Programmable high voltage supplies for laboratory and ATE applications

\$1350 (U.S. List)

- 25 Watts output power
- 0.001% regulation
- 0.05% accuracy
- Low output ripple
- Dual polarity
- Programmable voltage and current limits and trips
- Store and recall setups
- Full status display with voltage and current readouts
- Analog voltage programmable
- Optional IEEE-488 GPIB interface

The PS300 Series

| Model | Output Voltage | Current |
|-------|----------------------|---------|
| PS350 | 0 to ± 5.0 kVDC | 5 mA |
| PS325 | 0 to ± 2.5 kVDC | 10 mA |
| PS310 | 0 to ± 1.25 kVDC | 20 mA |

Introducing a new family of power supplies from Stanford Research Systems. The PS300 Series.

Rugged, compact programmable power supplies that fit just about any high voltage application.

And any budget.

Yet, even though the PS300 Series power supplies are priced economically, they outperform more expensive instruments and are loaded with features that make them more versatile and easier to use.

Choose from three models, with voltage to 5 kV and currents to 20 mA. All three have 25 Watts of output power with 0.001% regulation and 0.05% accuracy. And all of them are arc and short-circuit protected with separate, programmable hard and soft current limits, making it possible to use them as circuit breakers or constant current sources.


Whatever model you choose, you'll appreciate the convenience and versatility of the PS300 Series. Two LED displays monitor output voltage, current and polarity continuously. Overload reset, limit and trip status, local/remote state, and high voltage enable are also displayed, so you can monitor instrument status at a glance.

Operation is simple, too.

The parameter being adjusted or set is displayed separately and can be entered without affecting the actual output voltage. Up to 9 settings can be stored and recalled, making it easy to run multiple tests. Parameters are chosen using a SELECT key and set using either the number keys or the cursor keys on the keypad.

Unless, of course, you want remote operation.

Then, an optional IEEE-488 GPIB interface makes it possible to program and set



all PS300 Series operation modes remotely. All parameters can be set and read via the interface and Service Requests can be generated in response to overload or trip conditions. A rear panel switch allows the output voltage to be programmed by an analog input voltage and overrides both front panel and IEEE-488 programming.

All things considered, it's a lot to pack into a power supply that only measures 16" x 8" x 3.5"

But we wanted to make sure the PS300 Series works easily with your high voltage test procedures, analytical instruments, automatic test systems, and general laboratory applications.

To see exactly how well the PS300 Series fits your application, refer to the specifications on the back of this brochure. For further information, or to place an order, call Stanford Research Systems at (408) 744-9040.

Voltage and current displays provide 4 digit resolution plus polarity and can be read over the GPIB interface.

Entry display shows parameter value being set.

Overload response selects MANUAL or AUTOMATIC reset of high voltage after overload disable.

Entry Parameter and analog programming status display.



Front panel safety switch enables/disables the high voltage output and locks out GPIB control.


Store and recall up to 9 instrument setups.

Numeric or cursor entry

Limit, remote control (GPIB) and SRQ status displays.

Analog programming switch allows programming of output voltage by an analog input voltage. (Status is displayed on front panel.)

Polarity switch selects high voltage output polarity.



Optional GPIB Interface provides full remote instrument programmability and control.

Analog voltage and current monitor outputs provide 0 to 10 volts for 0 to full-scale outputs.

SHV high voltage output connector

Specifications

Output

| | |
|------------------------------|--|
| Voltage Set Accuracy | 0.01% + 0.05% of full scale |
| Voltage Display Accuracy | V Set Accuracy \pm 1 Volt (typ) |
| Voltage Resolution | 1 Volt (set & display) |
| Voltage Resettability | 1 Volt |
| Voltage Limit Range | 0 to 100% of full scale |
| Voltage Regulation | 0.001% for \pm 10% line voltage change; 0.005% for 100% load change. |
| Output Ripple | <0.0015% of full scale (Vrms typ) |
| Current Limit and Trip Range | 0 to 105% of full scale |
| Current Set Accuracy | 0.01% + 0.05% of full scale |
| Current Resolution | PS350 : 1 μ A; PS325, PS310 : 10 μ A |
| Current Display Accuracy | I Set Accuracy \pm 1 μ A (PS350) or 10 μ A (PS325 or PS310) (typ) |
| Stability | 0.01% per hour, <0.03% per 8 hours |
| Temperature Drift | 50 ppm/ C, 0 to 50 C (typ) |
| Protection | Arc and short circuit protected; programmable voltage and current limits and current trip. |
| Recovery Time | 12ms for 40% step change in load current (typ) |
| Discharge Time | <6 sec (to < 1% of full scale voltage with no load typ) |

Analog Programming

| | |
|-----------------------------|---|
| Remote Voltage Set | Remote Voltage setting is only enabled when the rear panel switch is in the REMOTE position. This disables both the front panel and GPIB voltage setting functions. |
| Range | 0 to +10 Volts sets 0 to full scale output. |
| Accuracy | 0.07% of full scale. |
| Update Rate | 16 Hz |
| Output Slew Rate | <0.30 sec for 0 to full scale under full load. |
| Voltage and Current Monitor | 0 to +10 Volts monitors 0 to full scale output. |
| Accuracy | 0.07% of full scale. |
| Update Rate | 8 Hz |

IEEE-488 GPIB Operation (Option 01)

| | |
|------------------------|---|
| Programmable Functions | Output Voltage, Output Voltage Limit, Current Limit, Current Trip, Reset Mode, Output Enable, Reset, SRQ Response Mode. |
| Readback Functions | Output Voltage, Output Current, Limit Settings, Status, Programming Error Codes, Error Condition, Service Request. |

General

| | |
|------------------|--|
| Display | 4 digit (plus sign) voltage display, 4 digit current display, 4 digit entry display, Indicator LEDs show HIGH VOLTAGE ON, Status and Remote State. |
| Output Connector | SHV high voltage |
| Dimensions | 16.0"X8.3"X3.5" |
| Weight | 8 lbs. |
| Power | 100, 120, 220, 240 Vac, 50 Watts |

All specifications and prices are subject to change (10/92)

Ordering Information

| | | |
|-------------|-----------------------------|--------|
| PS350 | 0 to \pm 5kV at 5 mA | \$1350 |
| PS325 | 0 to \pm 2.5kV at 10 mA | \$1350 |
| PS310 | 0 to \pm 1.25kV at 20 mA | \$1350 |
| Option 01. | IEEE-488 Computer interface | \$495 |
| Option 02S. | Rack Mount, Single | \$85 |
| Option 02D. | Rack Mount, Double | \$85 |
| Option 03A. | SHV to SHV Cable, 10 feet | \$50 |
| Option 03B. | SHV to MHV Cable, 10 feet | \$50 |



STANFORD RESEARCH SYSTEMS

1290 D Reamwood Avenue ■ Sunnyvale, CA 94089
Telephone: (408) 744-9040 ■ FAX: 4087449049

email: info@thinkSRS.com
Web: www.thinkSRS.com