

Signal Processing Blockset Release Notes

The “Signal Processing Blockset 6.0 Release Notes” on page 1-1 describe the changes introduced in the latest version of the Signal Processing Blockset. The following topics are discussed in these Release Notes.

- “New Features” on page 1-2
- “Major Bug Fixes” on page 1-12
- “Upgrading from an Earlier Release” on page 1-13
- “Known Software Problems” on page 1-14

The Signal Processing Blockset Release Notes also provide information about recent versions of the product, in case you are upgrading from a version that was released prior to Release 13 with Service Pack 1.

- “DSP Blockset 5.1 Release Notes” on page 2-1
- “DSP Blockset 5.0 Release Notes” on page 3-1
- “DSP Blockset 4.1 Release Notes” on page 4-1
- “DSP Blockset 4.0 Release Notes” on page 5-1

Printing the Release Notes

If you would like to print the Release Notes, you can link to a PDF version.



Signal Processing Blockset 6.0 Release Notes

1

New Features	1-2
Product Name Change	1-2
Additional Fixed-Point Support	1-2
New Blocks	1-5
Enhanced Blocks	1-7
Renamed Blocks	1-8
New Demos	1-9
Triggered Subsystem Support	1-10
Constant Sample Time Support	1-10
Source Blocks Obey New Simulink Inherited Sample Time Parameter	1-10
Signal & Scope Manager Support	1-10
Multitasking Support	1-11
Multirate Models	1-11
Scalar Quantizer Block Obsoleted	1-11
Major Bug Fixes	1-12
Upgrading from an Earlier Release	1-13
Known Software Problems	1-14

DSP Blockset 5.1 Release Notes

2

New Features	2-2
Additional Fixed-Point Support	2-2
Extended Adaptive Filter Support	2-4
Triggered Subsystem Support	2-4
New Blocks	2-5
Enhanced Blocks	2-6
New and Enhanced Demos	2-7
New Options for Delay Line Block	2-7

DSP Blockset 5.0 Release Notes

3

New Features	3-2
Full Single-Precision Support	3-3
Full Support of Embedded Real-Time (ERT) C Code Generation	3-3
Smaller, Faster Generated C Code That Requires Less RAM ..	3-3
Full Boolean Data Type Support	3-4
Expanding Fixed-Point Data Type Support	3-4
New Blocks	3-6
Enhanced Blocks	3-9
New and Enhanced Demos	3-14
Audio Blocks Relocated to New Block Library	3-15
New Options for Event Detection	3-15
 Major Bug Fixes	 3-17
 Upgrading from an Earlier Release	 3-18
New Default Setting Enables Boolean Data Type Support ...	3-19
Replaced Filtering Blocks	3-20
Wavelet Analysis and Wavelet Synthesis Blocks Replaced ...	3-20
Cumulative Sum Block Behaves Differently	3-21
Contiguous Copy Block Obsolete	3-21
Audio Blocks Relocated	3-21

DSP Blockset 4.1 Release Notes

4

New Features	4-2
New Digital Filter Design Block	4-2
Major Individual Block Enhancements	4-2
Blocks with Enhanced Data Type Support	4-5
Blocks with Tunability Enhancements	4-6
Enhancements to Blocks Implemented with S-Functions	4-7
Real-Time Workshop Generated C Code Enhancements	4-8
Changes to Filtering Block Libraries	4-9
Major Bug Fixes	4-10
Real-Time Workshop C Code Generated from DSP Blockset ..	4-10
Nontunable Block Parameters	4-10
Chirp Block	4-10
Matrix Viewer Block	4-10
Random Source Block	4-11
Stack and Queue Blocks	4-11
Window Function Block	4-11
Upgrading from an Earlier Release	4-12

DSP Blockset 4.0 Release Notes

5

New Features	5-2
Matrix Support	5-2
Frame Support	5-4
New and Enhanced Blocks	5-5
Library Reorganization	5-7
Upgrading from an Earlier Release	5-12
Adding Release 12 Blocks to Release 11 Models	5-12

Signal Processing Blockset 6.0 Release Notes

New Features	1-2
Product Name Change	1-2
Additional Fixed-Point Support	1-2
New Blocks	1-5
Enhanced Blocks	1-7
Renamed Blocks	1-8
New Demos	1-9
Triggered Subsystem Support	1-10
Constant Sample Time Support	1-10
Source Blocks Obey New Simulink Inherited Sample Time Parameter	1-10
Signal & Scope Manager Support	1-10
Multitasking Support	1-11
Multirate Models	1-11
Scalar Quantizer Block Obsoleted	1-11
Major Bug Fixes	1-12
Upgrading from an Earlier Release	1-13
Known Software Problems	1-14

New Features

This section introduces the new features and enhancements added to the Signal Processing Blockset 6.0 (Release 14) since DSP Blockset 5.1 (Release 13 SP1):

- “Product Name Change” on page 1-2
- “Additional Fixed-Point Support” on page 1-2
- “New Blocks” on page 1-5
- “Enhanced Blocks” on page 1-7
- “Renamed Blocks” on page 1-8
- “New Demos” on page 1-9
- “Triggered Subsystem Support” on page 1-10
- “Constant Sample Time Support” on page 1-10
- “Source Blocks Obey New Simulink Inherited Sample Time Parameter” on page 1-10
- “Signal & Scope Manager Support” on page 1-10
- “Multitasking Support” on page 1-11
- “Multirate Models” on page 1-11
- “Scalar Quantizer Block Obsoleted” on page 1-11

If you are upgrading from a release earlier than Release 13 SP1, then you should see of the “DSP Blockset 5.1 Release Notes” on page 2-1.

Product Name Change

The DSP Blockset has been renamed. The new name is the Signal Processing Blockset.

Additional Fixed-Point Support

For this release, significant support for fixed-point development has been added to the Signal Processing Blockset.

For a complete list of all blocks in the Signal Processing Blockset that support fixed-point data types, refer to “Blocks with Fixed-Point Support” in the Signal Processing Blockset User’s Guide.

New Fixed-Point Blocks

The following new blocks support fixed-point data types:

- CIC Decimation
- CIC Interpolation
- Offset
- Peak Finder
- Scalar Quantizer Decoder
- Scalar Quantizer Encoder
- Vector Quantizer Decoder
- Vector Quantizer Encoder
- Zero Crossing

Blocks with Added Fixed-Point Support

The following blocks now support fixed-point data types:

- Constant Ramp
- Cumulative Product
- Cumulative Sum
- Difference
- Digital Filter — more structures now support fixed-point data types
- FIR Rate Conversion
- Histogram
- Levinson-Durbin
- LMS Filter
- Matrix 1-Norm
- Matrix Scaling
- Mean
- Median
- Normalization
- Short-Time FFT
- Signal From Workspace
- Signal To Workspace

- Sort
- Triggered Signal From Workspace
- Triggered To Workspace
- Toeplitz
- Two-Channel Analysis Subband Filter
- Two-Channel Synthesis Subband Filter

Fixed-Point Blocks with New Complex Support

The following blocks supported real fixed-point data types in the last major release. They now also support complex fixed-point data types:

- Autocorrelation
- Convolution
- Correlation
- FIR Decimation
- FIR Interpolation
- Sort

Fixed-Point Blocks with a New Interface

Many of the Signal Processing Blockset blocks that support fixed-point data types have a new, easier-to-use interface. For more information, see “Setting Block Parameters” in the Signal Processing Blockset User’s Guide.

New Automatic Selection of Fixed-Point Word and Fraction Lengths

Many blocks with fixed-point support in the Signal Processing Blockset allow you to set intermediate data types via block mask parameters. The **Accumulator**, **Product output**, and **Output** parameters on many such blocks have a new `Inherit via internal rule` setting. When you select `Inherit via internal rule`, the accumulator, product output, or block output word and fraction lengths will be automatically calculated for you. In general, all the bits are preserved in the internal block algorithm for quantities using this selection. That is, the accumulator, product output, or block output word and fraction lengths are selected such that

- No overflow occurs.
- No precision loss occurs.

Internal rule equations specific to each block are given in the block reference pages.

New Logging of Simulation Minimums and Maximums and Autoscaling

A number of fixed-point blocks in the Signal Processing Blockset now support the logging of simulation minimums and maximums and autoscaling via the Fixed-Point Settings interface. Refer to “Fixed-Point Settings Interface” in the Signal Processing Blockset User’s Guide for more information.

New Blocks

A summary of the new blocks is presented below:

- CIC Decimation and CIC Interpolation
- G711 Codec
- Inverse Short-Time FFT
- LPC to/from Cepstral Coefficients
- Offset
- Peak Finder
- Scalar Quantizer Decoder
- Scalar Quantizer Encoder
- Short-Time FFT
- Vector Quantizer Decoder
- Vector Quantizer Design
- Vector Quantizer Encoder
- Waterfall Scope
- Zero Crossing

CIC Decimation and CIC Interpolation

The CIC Decimation and CIC Interpolation blocks are in the Filtering/Multirate Filters library. These blocks decimate or interpolate a signal using a Cascaded Integrator-Comb filter.

G711 Codec

The G711 Codec block is in the Quantizers library. This block encodes a linear, pulse code modulation (PCM) narrowband speech signal using an A-law or mu-law encoder. The block decodes index values into quantized output values using an A-law or mu-law decoder. The block converts between A-law and mu-law index values.

Inverse Short-Time FFT

The Inverse Short-Time FFT block is in the Transforms library. This block recovers the time-domain signal by performing an inverse short-time, fast Fourier transform operation.

LPC to/from Cepstral Coefficients

The LPC to/from Cepstral Coefficients block is in the Linear Prediction library. This block converts linear prediction coefficients (LPCs) to cepstral coefficients (CCs) or cepstral coefficients to linear prediction coefficients.

Offset

The Offset block is in the Signal Operations library. This block truncates vectors by removing or keeping beginning or ending values.

Peak Finder

The Peak Finder block is in the Signal Operations library. This block finds the local maxima and/or minima of an input signal.

Scalar Quantizer Decoder

The Scalar Quantizer Decoder block is in the Quantizers library. This block converts each index value into a quantized output value.

Scalar Quantizer Encoder

The Scalar Quantizer Encoder block is in the Quantizers library. This block encodes each input value by associating it with the index value of a quantization region.

Short-Time FFT

The Short-Time FFT block is in the Transforms library. This block computes a nonparametric estimate of the spectrum using the short-time, fast Fourier

transform method. The Short-Time FFT block that was located in the Power Spectrum Estimation library has been renamed the Periodogram block.

Vector Quantizer Decoder

The Vector Quantizer Decoder block is in the Quantizers library. This block finds the vector quantizer codeword that corresponds to a given, zero-based index value.

Vector Quantizer Design

The Vector Quantizer Design block is in the Quantizers library. This block designs a vector quantizer using the Vector Quantizer Design Tool (VQDTool).

Vector Quantizer Encoder

The Vector Quantizer Encoder block is in the Quantizers library. This block finds the index of the nearest codeword based on a Euclidean or weighted Euclidean distance measure.

Waterfall Scope

The Waterfall Scope block is in the DSP Sinks library. This block enables you to view vectors of data over time.

Zero Crossing

The Zero Crossing block is in the Signal Operations library. This block counts the number of times a signal crosses zero.

Enhanced Blocks

For descriptions of the enhanced blocks, see the following sections:

- “Counter” on page 1-8
- “Digital Filter” on page 1-8
- “Matrix Viewer” on page 1-8
- “Scalar Quantizer Design” on page 1-8
- “Sort” on page 1-8

Counter

The **Count data type** parameter of the Counter block now supports signed and unsigned integers.

Digital Filter

The Digital Filter block now supports these additional filter structures:

- FIR
 - Direct form symmetric
 - Direct form antisymmetric
- IIR Biquad (SOS)
 - Direct form I
 - Direct form I transposed
 - Direct form II

Every filter structure now supports fixed-point data types.

Biquad (SOS) filter structures support interstage floating-point and fixed-point scale values.

Matrix Viewer

The Matrix Viewer block parameters dialog box has been upgraded.

Scalar Quantizer Design

You can now use the Scalar Quantizer Design Tool to create Scalar Quantizer Encoder and Scalar Quantizer Decoder blocks inside your models.

Sort

The Sort block now supports an additional sorting algorithm. Now, for the **Sort algorithm** parameter, you can choose either **Quick sort** or **Insertion sort**. Previously, only the quick sort algorithm was supported.

Renamed Blocks

Periodogram

The Short-Time FFT block that was located in the Power Spectrum Estimation library has been renamed the Periodogram block. This block computes a

nonparametric estimate of the spectrum. All instances of the old Short-Time FFT block have been replaced by the Periodogram block.

New Demos

Demo Name	Signal Processing Demo Library Location	Launch Command
Adaptive filter convergence	Adaptive Processing	lmsxyplot
CELP speech coder	Audio Processing	dspcelpcoder
G711 A-law and A-Mu-A conversion	Audio Processing	dspg711amua
G711 Mu-law and Mu-A-Mu conversion	Audio Processing	dspg711muamu
G711 and PCM encoding	Audio Processing	dspg711cmp
Phase vocoder	Audio Processing	dsppitchtime
Plucked string	Audio Processing	dsppluck
Radar tracking demonstration	Aerospace	aero_radmod_dsp
Short-Time Spectral Attenuation	Spectral Analysis	dspstsa
Vector quantizer design	Miscellaneous	dspvqtwodim

The Short-Time FFT demo in Spectral Analysis demo library is now the Periodogram demo.

The Acoustic Noise Canceler demo (dspanc) is now supported on all platforms. It also has a fixed-point version (dspanc_fixpt).

The Signal Processing Blockset has a new demo library called Fixed-Point. This library contains demo models that support fixed-point data types.

Triggered Subsystem Support

Signal Processing Blockset blocks now support triggered subsystems. The exceptions are

- Chirp block
- Multiphase Clock
- Sine Wave block
- Blocks with multiple sample times

Constant Sample Time Support

The Signal Processing Blockset has extended support of constant sample times to its blocks. The output of blocks with constant sample times does not change during the simulation. You can remove all blocks having constant sample times from the simulation “loop” by setting the **Inline parameters** option. If you select the **Inline parameters** check box on the **Optimization** pane of the **Configuration** dialog box, the parameters of these blocks cannot be changed during a simulation, and simulation speed is improved.

Source Blocks Obey New Simulink Inherited Sample Time Parameter

Signal Processing Blockset source blocks capable of inheriting their sample time obey a new Simulink inherited sample time parameter. To view this parameter, open the **Configuration** dialog box. In the **Select** pane, expand **Diagnostics** and click **Sample Time**. The new parameter, **Source block specifies -1 sample time** appears in the left pane. This parameter can be set to none, warning (default), or error.

The Random Source block is the only block that does not obey this parameter. If its **Sample time** parameter is set to -1, the Random Source block inherits its sample time from its output port and never produces warnings or errors.

Signal & Scope Manager Support

You can use the Signal & Scope Manager to create and view signals without using blocks. The Signal Processing Blockset provides signal generators and viewers that you can associate with your model using the Signal & Scope Manager. To view these generators and viewers, right-click in your model, and

select **Signal & Scope Manager**. From the **Generators** and **Viewers** lists, expand **Signal Processing**.

For information on how to use the Signal & Scope Manager, see “The Signal & Scope Manager” in the Simulink documentation.

Multitasking Support

If you have a multirate model that you want to run in `MultiTasking` mode and your model contains any of the blocks listed below, your reset event can be delayed as much as one reset time interval so your model behaves deterministically:

- Minimum
- Maximum
- Mean
- Standard Deviation
- Variance
- RMS
- Cumulative Sum
- Cumulative Product
- Delay

To minimize delay in multirate models, run them in `SingleTasking` mode.

Multirate Models

The following blocks no longer support different sample rates at their input ports:

- Permute Matrix
- Variable Selector
- Variable Integer Delay

Scalar Quantizer Block Obsoleted

The Scalar Quantizer block has been replaced by the Scalar Quantizer Encoder and Scalar Quantizer Decoder blocks.

Major Bug Fixes

The Signal Processing Blockset 6.0 includes several bug fixes made since Version 5.1. This section describes the important Version 6.0 bug fixes.

If you are viewing these Release Notes in PDF form, please refer to the HTML form of the Release Notes, using either the Help browser or the MathWorks Web site and use the link provided.

Upgrading from an Earlier Release

This section describes issues involved in migrating DSP Blockset Version 2.2 and earlier models to the Signal Processing Blockset Version 6.0 environment.

As of Version 6.0 (Release 14) of the Signal Processing Blockset, DSP Blockset Versions 2.2 (Release 10) and earlier are obsolete and no longer supported. Models that contain blocks from Versions 2.2 and earlier will have broken links when loaded into Simulink 6.0 (Release 14).

If you have models that contain blocks from DSP Blockset Versions 2.2 or earlier, replace the older blocks by blocks from DSP Blockset Versions 4.0 (Release 12) or later before upgrading to Signal Processing Blockset 6.0 (Release 14). Use the command `dsp_links` to facilitate this process.

DSP Blockset Version 3.x (Release 11) might also be obsoleted in a future release.

Known Software Problems

This section includes a link to a description of known software and documentation problems in Version 6.0.

If you are viewing these Release Notes in PDF form, please refer to the HTML form of the Release Notes, using either the Help browser or the MathWorks Web site and use the link provided.

DSP Blockset 5.1 Release Notes

New Features	2-2
Additional Fixed-Point Support	2-2
Extended Adaptive Filter Support	2-4
Triggered Subsystem Support	2-4
New Blocks	2-5
Enhanced Blocks	2-6
New and Enhanced Demos	2-7
New Options for Delay Line Block	2-7

New Features

This section introduces the new features and enhancements added to the DSP Blockset 5.1 since DSP Blockset 5.0 (Release 13).

The new features discussed in this section are:

- “Additional Fixed-Point Support” on page 2-2
- “Extended Adaptive Filter Support” on page 2-4
- “Triggered Subsystem Support” on page 2-4
- “New Blocks” on page 2-5
- “Enhanced Blocks” on page 2-6
- “New and Enhanced Demos” on page 2-7
- “New Options for Delay Line Block” on page 2-7

If you are upgrading from a release earlier than Release 13, then you should see “New Features” on page 3-2 of the Release Notes for DSP Blockset 5.0.

Additional Fixed-Point Support

For this release, significant support for fixed-point development has been added to the DSP Blockset.

Blocks

Fixed-point support has been added to key blocks essential for the modeling of fixed-point DSP systems. These blocks support the processing of signed fixed-point quantities in both simulation and code generation. Supported word sizes are from 2 to 128 bits in simulation, and from 2 to the size of a long on the intended target for code generation. The following table lists all DSP Blockset blocks that currently support fixed-point signals. These blocks are colored orange in the DSP Blockset library.

Autocorrelation	Buffer	Check Signal Attributes	Constant Diagonal Matrix
Convert 1-D to 2-D	Convert 2-D to 1-D	Convolution	Correlation

Counter	Create Diagonal Matrix	Data Type Conversion (Simulink block)	Delay Line
Digital Filter	Discrete Impulse	Display (Simulink block)	Downsample
DSP Constant	DSP Fixed-Point Attributes	DSP Gain	DSP Product
DSP Sum	Edge Detector	Event-Count Comparator	Extract Diagonal
Extract Triangular Matrix	FFT	Filter Realization Wizard	FIR Decimation
FIR Interpolation	Flip	Frame Status Conversion	Identity Matrix
IFFT	Integer Delay	Matrix Concatenation (Simulink block)	Matrix Product
Matrix Scaling	Matrix Sum	Matrix Viewer	Maximum
Minimum	Multiphase Clock	Multiport Selector	N-Sample Enable
N-Sample Switch	Overwrite values	Pad	Permute Matrix
Queue	Repeat	Sample and Hold	Selector (Simulink block)
Signal To Workspace	Sine Wave	Spectrum Scope	Stack
Submatrix	Time Scope (Simulink block)	Toeplitz	Transpose
Triggered Delay Line	Triggered to Workspace	Unbuffer	Upsample
Variable Integer Delay	Variable Selector	Vector Scope	Window Function
Zero Pad			

Many of the above blocks that perform arithmetic calculations, such as Digital Filter and FFT, now allow you to specify intermediate fixed-point data types on their block mask. The ability to configure these parameters, such as accumulator and product output data type parameters, allows you to more closely simulate your target hardware. Refer to “Setting Block Parameters” in Chapter 6 of the DSP Blockset documentation for more information.

System-Level Control

The new DSP Fixed-Point Attributes (DFPA) block gives you access to a GUI that allows you to set fixed-point parameters for DSP blockset blocks on a system or subsystem level. This allows you to specify fixed-point attributes for large groups of blocks at one time, without having to individually configure the parameters on each block mask. The word and fraction lengths of fixed-point data types, as well as overflow handling and rounding methods, can be set using DFPA blocks. Refer to the DSP Fixed-Point Attributes block reference page in the DSP Blockset documentation for more information.

Extended Adaptive Filter Support

The LMS Filter and RLS Filter blocks have replaced the LMS Adaptive Filter and RLS Adaptive Filter blocks. The LMS Filter block is designed to support five different types of LMS algorithms. In addition, two other blocks, the Block LMS Filter and the Fast Block LMS Filter, have been added to the Adaptive Filters library. All of the new adaptive filter blocks support frame-based processing.

For more information, see the LMS Filter, RLS Filter, Block LMS Filter, and Fast Block LMS Filter block reference pages.

Triggered Subsystem Support

Almost all of the DSP Blockset blocks are now supported in triggered subsystems. Triggered subsystems do not support the following blocks:

- Overlap-Add FFT Filter
- Overlap-Save FFT Filter
- Unbuffer

New Blocks

For descriptions of the new blocks, see the following sections:

- “DSP Fixed-Point Attributes” on page 2-5
- “DSP Gain” on page 2-5
- “DSP Product” on page 2-5
- “DSP Sum” on page 2-5
- “LPC to/from RC” on page 2-5
- “LPC/RC to Autocorrelation” on page 2-6
- “Matrix Exponential” on page 2-6
- “Scalar Quantizer” on page 2-6
- “Scalar Quantizer Design” on page 2-6

DSP Fixed-Point Attributes

The DSP Fixed-Point Attributes block is in the Signal Attributes library. This block sets fixed-point attributes of DSP Blockset blocks on the system or subsystem level.

DSP Gain

The DSP Gain block is in the Math Operations library. This block multiplies the input by a constant. The DSP Gain block has fixed-point support.

DSP Product

The DSP Product block is in the Math Operations library. This block performs element-wise multiplication of two inputs. The DSP Product block has fixed-point support.

DSP Sum

The DSP Sum block is in the Math Operations library. This block adds two inputs. The DSP Sum block has fixed-point support.

LPC to/from RC

The LPC to/from RC block is in the Linear Prediction library. This block converts linear prediction coefficients to reflection coefficients or reflection coefficients to linear prediction coefficients.

LPC/RC to Autocorrelation

The LPC/RC to Autocorrelation block is in the Linear Prediction library. This block converts linear prediction coefficients or reflection coefficients to autocorrelation coefficients.

Matrix Exponential

The Matrix Exponential block is in the Matrix Operations library. It computes the matrix exponential.

Scalar Quantizer

The Scalar Quantizer block is in the Quantizers library. It converts an input signal into a set of index values or a set of quantized output values. It can also convert a set of index values into a quantized output signal.

Scalar Quantizer Design

The Scalar Quantizer Design block is in the Quantizers library. You can use this block to start the Scalar Quantizer Design Tool (SQDTool) to design a scalar quantizer using the Lloyd algorithm.

Enhanced Blocks

The following blocks have improved functionality for DSP Blockset 5.1.

Delay Block

The Delay block has replaced the Integer Delay block in the Signal Operations library. The Delay block is optimized with an improved user-interface that makes it easier to specify initial conditions. In addition, the block has been optimized for computational complexity.

From Wave File Block

The From Wave File Block now supports the repeated output of audio files. You can now play your .wav file more than once.

Blocks with Added Fixed-Point Support

These DSP Blockset blocks now support fixed-point data types.

Autocorrelation	Convolution	Correlation
Digital Filter	Event-Count Comparator	FFT
FIR Decimation	FIR Interpolation	IFFT
Matrix Product	Matrix Scaling	Matrix Sum
Window Function		

New and Enhanced Demos

The Adaptive Noise Cancellation Demo was added to the DSP Demos. Run this demo by typing `dspanc` in the MATLAB Command Window. To learn more about this demo, see “Creating an Acoustic Environment” in the DSP Blockset documentation.

Any demos that contained the LMS Adaptive Filter or RLS Adaptive Filter blocks have been upgraded to use the new LMS Filter and RLS Filter blocks.

New Options for Delay Line Block

You now have the option of either feeding the input through the block directly, or imposing a one sample or one frame delay.

DSP Blockset 5.0 Release Notes

New Features	3-2
Full Single-Precision Support	3-3
Full Support of Embedded Real-Time (ERT) C Code Generation	3-3
Smaller, Faster Generated C Code That Requires Less RAM	3-3
Full Boolean Data Type Support	3-4
Expanding Fixed-Point Data Type Support	3-4
New Blocks	3-6
Enhanced Blocks	3-9
New and Enhanced Demos	3-14
Audio Blocks Relocated to New Block Library	3-15
New Options for Event Detection	3-15
 Major Bug Fixes	 3-17
 Upgrading from an Earlier Release	 3-18
New Default Setting Enables Boolean Data Type Support	3-19
Replaced Filtering Blocks	3-20
Wavelet Analysis and Wavelet Synthesis Blocks Replaced	3-20
Cumulative Sum Block Behaves Differently	3-21
Contiguous Copy Block Obsolete	3-21
Audio Blocks Relocated	3-21

New Features

This section introduces the new features and enhancements added to the DSP Blockset 5.0 (Release 13) since DSP Blockset 4.1 (Release 12.1).

If you are upgrading from a release earlier than Release 12.1, then you should see “New Features” on page 4-2 of the Release Notes for DSP Blockset 4.1.

Two major new features of DSP Blockset 5.0 include the following:

- Full single-precision support in all blocks
- Full support of the embedded real-time (ERT) generated ANSI C code (requires the Real-Time Workshop Embedded Coder)

For details about these and other new features and enhancements, see the following topics:

- “Full Single-Precision Support” on page 3-3
- “Full Support of Embedded Real-Time (ERT) C Code Generation” on page 3-3
- “Smaller, Faster Generated C Code That Requires Less RAM” on page 3-3
- “Full Boolean Data Type Support” on page 3-4
- “Expanding Fixed-Point Data Type Support” on page 3-4
- “New Blocks” on page 3-6
- “Enhanced Blocks” on page 3-9
- “New and Enhanced Demos” on page 3-14
- “Audio Blocks Relocated” on page 3-21
- “New Options for Event Detection” on page 3-15

The increased support for single-precision computation and ERT code generation, together with other major enhancements, provide an efficient solution for the design and implementation of complete, high-performance floating-point DSP systems.

Full Single-Precision Support

All DSP Blockset blocks now support single-precision floating-point computation in both simulation and Real-Time Workshop C code generation.

To learn more about data type support in the DSP Blockset, see the topic on data type support in the DSP Blockset documentation.

Full Support of Embedded Real-Time (ERT) C Code Generation

All DSP Blockset blocks now support embedded real-time (ERT) ANSI C code generation (requires the Real-Time Workshop Embedded Coder).

Smaller, Faster Generated C Code That Requires Less RAM

Real-Time Workshop (RTW) ANSI C code generated from DSP Blockset blocks is now smaller, faster, and requires less RAM, largely due to the following enhancements:

- **Function reuse (run-time libraries)** — The code generated from most blocks now *reuses* common algorithmic functions from ANSI C run-time libraries, leading to smaller generated code. In addition, the functions in the run-time libraries are highly optimized, resulting in faster generated code that requires less RAM.
- **Parameter reuse (RTW run-time parameters)** — For most blocks, if there are multiple instances of a block that all have the same value for a specific parameter, each block instance points to the same variable in the generated code, thereby reducing memory requirements.

Full Boolean Data Type Support

All block input ports that accept logical signals now support the Boolean data type. In addition, for all outputs that are logical signals, the default data type is now Boolean.

For a list of DSP Blockset blocks that support Boolean data types, see the topic on Boolean data type support in the DSP Blockset documentation.

In some cases, you may want to override the Simulink default and *disable* Boolean support, as described in “New Default Setting Enables Boolean Data Type Support” on page 3-19. For more information about disabling Boolean support, see the following topics in the DSP Blockset documentation:

- Steps to disable Boolean support
- The effects of enabling and disabling Boolean support

Expanding Fixed-Point Data Type Support

The DSP Blockset 5.0 includes more blocks that support fixed-point data types, including some source blocks. Support of fixed-point data types will continue to expand in future releases.

The following blocks are all the blocks in the DSP Blockset that support fixed-point data types. You can use all of these blocks with Fixed-Point Blockset blocks, and with Simulink blocks that support fixed-point data types. These blocks are colored orange in the DSP Blockset library. (Some of the blocks are Simulink blocks that are available in the DSP Blockset libraries as well as the Simulink libraries.)

To take full advantage of DSP Blockset fixed-point capabilities, you must install the Fixed-Point Blockset. For more information, see the topic on licensing information in the Fixed-Point Blockset documentation.

For more information on the DSP Blockset blocks that support fixed-point, see the topic on fixed-point support in the DSP Blockset documentation.

- Buffer
- Check Signal Attributes
- Constant Diagonal Matrix
- Convert 1-D to 2-D
- Convert 2-D to 1-D
- Create Diagonal Matrix
- Data Type Conversion (Simulink block)
- Delay Line
- Discrete Impulse
- Display (Simulink block)
- Downsample
- DSP Constant
- Edge Detector
- Extract Diagonal
- Extract Triangular Matrix
- Filter Realization Wizard
- Flip
- Frame Status Conversion
- Identity Matrix
- Inherit Complexity
- Integer Delay
- Matrix Concatenation (Simulink block)
- Matrix Viewer
- Maximum
- Minimum
- Multiphase Clock
- Multiport Selector
- N-Sample Enable
- N-Sample Switch
- Overwrite values
- Pad
- Permute Matrix
- Queue
- Repeat
- Sample and Hold
- Selector (Simulink block)
- Signal To Workspace
- Sine Wave
- Spectrum Scope
- Stack
- Submatrix
- Time Scope (Simulink block)
- Toeplitz
- Transpose
- Triggered Delay Line
- Triggered To Workspace
- Unbuffer
- Upsample
- Variable Integer Delay
- Variable Selector
- Vector Scope
- Zero Pad

New Blocks

The key new block for Release 13 is the Digital Filter block. For descriptions of this and other new blocks and links to their online reference pages, see the following sections:

- “Cumulative Product” on page 3-6
- “Digital Filter” on page 3-6
- “DWT and IDWT” on page 3-7
- “Interpolation” on page 3-7
- “LPC to LSF/LSP Conversion and LSF/LSP to LPC Conversion” on page 3-7
- “Overwrite Values” on page 3-8
- “Two-Channel Analysis Subband Filter and Two-Channel Synthesis Subband Filter” on page 3-8

Cumulative Product

The new Cumulative Product block is in the Math Operations library. This block computes the cumulative product of the row or column elements of the input matrix.

Digital Filter

The new Digital Filter block in the Filter Designs library is ideal for implementing digital filters that you have already designed. The block supports a variety of filter structures, and can implement *static filters* with fixed coefficients, as well as *time-varying filters* with coefficients that change over time. Using the filter you specify, the block individually filters each channel of the input signal and outputs the result. The block’s output numerically matches the output of the `filter` function in the Filter Design Toolbox and the `filter` function in the Signal Processing Toolbox.

You can use the Digital Filter block to efficiently simulate the numerical behavior of your filter on a single- or double-precision floating-point system such as a personal computer or DSP chip. You can also use the block to generate highly optimized Real-Time Workshop ANSI C code for use in single- and double-precision floating-point embedded systems. (Note that

To implement a filter with the Digital Filter block, you must provide the following basic information about your filter:

- Whether the filter transfer function is FIR with all zeros, IIR with all poles, or IIR with poles and zeros
- The desired filter structure
- The filter coefficients (entered as a parameter, or from an additional port, which is useful for time-varying filters)

The block supports the following filter structures:

- Direct form
- Direct form I
- Direct form II
- Transposed direct form
- Direct form I transposed
- Direct form II transposed
- Biquadratic direct form II transposed (second order sections)
- Lattice AR
- Lattice MA

DWT and IDWT

The new DWT block in the Transforms library computes the discrete wavelet transform (DWT) of its input. The IDWT block computes the *inverse* DWT of its input. These blocks are identical to the Dyadic Analysis Filter Bank and Dyadic Synthesis Filter Bank blocks in the Multirate Filters library.

The DWT block uses a filter bank with specified highpass and lowpass FIR filters to decompose the input signal into subbands that have smaller bandwidths and slower sample rates. Similarly, the IDWT block uses a filter bank to reconstruct the original signal from the subbands output by the DWT block.

The filter bank filters in both blocks can be user-defined or wavelet-based. Use of wavelet-based filters requires the Wavelet Toolbox.

Interpolation

The new Interpolation block in the Signal Operations library interpolates real-valued input signals at points between sample times by using linear or FIR interpolation. You specify the times at which the block should interpolate points, and the block outputs the interpolated values.

LPC to LSF/LSP Conversion and LSF/LSP to LPC Conversion

The new LPC to LSF/LSP Conversion block and LSF/LSP to LPC Conversion block in the Linear Prediction library are ideal for speech applications such as

speech coding and speech recognition. The first block allows you to convert linear prediction coefficients (LPCs) to line spectral pairs (LSPs) or line spectral frequencies (LSFs). The second block converts LSFs or LSPs back to LPCs. When converting LPCs, you can adjust the accuracy of the LSF or LSP output and set the block to flag invalid outputs due to unstable polynomial inputs.

Overwrite Values

The new Overwrite Values block in the Matrix Operations library overwrites either a specified submatrix of the input matrix or a specified portion of the input's main diagonal.

Two-Channel Analysis Subband Filter and Two-Channel Synthesis Subband Filter

The new Two-Channel Analysis Subband Filter block in the Multirate Filters library decomposes a signal into a high-frequency subband and a low-frequency subband using the specified highpass and lowpass FIR filters. Each subband has half the bandwidth and half the sample rate of the original signal.

Similarly, the new Two-Channel Synthesis Subband Filter block uses a filter bank to reconstruct the original signal from the high-frequency and a low-frequency subbands output by the Two-Channel Analysis Subband Filter block.

Enhanced Blocks

For summaries of individual block enhancements for Release 13 and links to their online reference pages, see the following sections:

- “Audio Blocks — New 24- and 32-Bit Support” on page 3-9
- “Autocorrelation, Correlation, Convolution — New Optimization Options” on page 3-10
- “Cumulative Sum — Intraframe Running Sums of Frame-Based Columns” on page 3-10
- “DCT and IDCT — New Optimization Options” on page 3-10
- “Digital Filter Design — Supports More Filter Structures” on page 3-10
- “Dyadic Analysis Filter Bank and Dyadic Synthesis Filter Bank Enhancements” on page 3-11
- “Filter Realization Wizard — New Filter Design Options, Better Fixed-Point Support, More Structures” on page 3-11
- “Random Source — Better Random Signals and New Option” on page 3-13
- “Sine Wave — Accepts Zero and Negative Frequencies” on page 3-13

Audio Blocks — New 24- and 32-Bit Support

The To Wave Device and From Wave Device blocks now support 24-bit audio devices in addition to 8- and 16-bit audio devices.

The To Wave File and From Wave File blocks now support 24 bits per sample and 32 bits per sample in addition to the previous 8- and 16-bit support.

All four audio blocks are now located in a new library. For more information, see “Audio Blocks Relocated” on page 3-21.

Autocorrelation, Correlation, Convolution — New Optimization Options

The Autocorrelation, Correlation, and Convolution blocks used to compute only in the time domain. Now you can set their computation domains to one of the following:

- **Time domain** — Minimizes memory use
- **Frequency domain** — Depending on the input length, may require fewer computations than computing in the time domain

The Correlation and Convolution blocks also have a third computation domain option, **Fastest domain**, which computes in the domain that minimizes the number of computations (time domain or frequency domain). The Autocorrelation block does not yet support this option.

Cumulative Sum — Intraframe Running Sums of Frame-Based Columns

The Cumulative Sum block can now compute a running sum of each column of a frame-based input, independent of the running sum of columns of previous inputs.

DCT and IDCT — New Optimization Options

The DCT and IDCT blocks use sine and cosine values to compute the discrete cosine transform and its inverse. You can now set the blocks to compute sines and cosines in one of the following ways:

- **Table lookup** — Look up sine and cosine values in a speed-optimized table
- **Trigonometric function calls** — Make sine and cosine function calls

Digital Filter Design — Supports More Filter Structures

The Digital Filter Design block, which previously supported only the direct form II transposed structure, now supports all of the following structures:

- Direct form I
- Direct form II
- Direct form I transposed
- Direct form II transposed
- Direct form FIR
- Direct form FIR transposed

Dyadic Analysis Filter Bank and Dyadic Synthesis Filter Bank Enhancements

The Dyadic Analysis Filter Bank block and Dyadic Synthesis Filter Bank block (referred to as “analysis block” and “synthesis block”) share several changes and enhancements described below.

New Wavelet Option. Both blocks now allow you to specify wavelet-based highpass and lowpass filters in addition to the previously supported user-defined filters. Use of wavelets requires the Wavelet Toolbox.

New Option for Single-Port Inputs and Outputs. Previously, the analysis block output each subband on a separate output port and the synthesis block accepted each subband through a separate input port. Now the analysis block provides an option to output a single vector or matrix of concatenated subbands, and the synthesis block provides an option to accept such inputs through a single input port.

Frame-Based Support Only. The analysis block now accepts only frame-based input signals. The synthesis block now always outputs frame-based signals. To decompose or reconstruct a sample-based signal using filter banks, you can create your own filter banks using the new Two-Channel Analysis Subband Filter and Two-Channel Synthesis Subband Filter blocks in the Multirate Filters library (see “Two-Channel Analysis Subband Filter and Two-Channel Synthesis Subband Filter” on page 3-8).

Filter Realization Wizard —

New Filter Design Options, Better Fixed-Point Support, More Structures

The Filter Realization Wizard block has several significant enhancements described below.

New Interface Provides Filter Design and Analysis Options. The Filter Realization Wizard block interface is now a part of the Filter Design and Analysis Tool (FDATool) GUI. Previously, the block required you to specify the filter by typing in its coefficients (you had to predesign the filter elsewhere). You now have the option to design your filter within the block; the extensive set of filter design and analysis tools in FDATool allow the block to automatically implement your filter design without you having to type its coefficients.

Enhanced Fixed-Point Support. The Filter Realization Wizard block now better supports fixed-point filters due to the following enhancements:

- **New fixed-point filter design capabilities** — The block now allows you to design fixed-point filters by using the **Set Quantization Parameters** panel in the new block interface. Use of this panel requires the Filter Design Toolbox.
- **Better fixed-point filter implementation** — The block now implements a much better fixed-point filter when you install the Fixed-Point Blockset and Filter Design Toolbox. To implement a good fixed-point filter, you should first design a fixed-point filter as described above and then set the block to implement the filter using Fixed-Point Blockset blocks.

Corresponding `dfilt` and `qfilt` Methods. `dfilt` (`dfilt.calattice` and `dfilt.calatticepc`) and `qfilt` objects now have a new `realizemdl` method. This method allows you to access the filter realization capabilities of the Filter Realization Wizard block from the command line.

Supports More Filter Structures. The block can now realize filters using any of the following filter structures:

- Direct form I
- Direct form II
- Direct form I transposed
- Direct form II transposed
- Second order sections for direct form I and II, and their transposes
- Direct form FIR
- Direct form FIR transposed
- Direct form asymmetric FIR
- Direct form symmetric FIR
- Lattice ARMA
- Lattice AR
- Lattice MA (same as lattice minimum phase)
- Lattice all-pass
- Lattice maximum phase
- Cascade
- Parallel

You may not be able to directly access some of the above structures through the block interface, but you *can* access all of them by creating a `qfilt` or `dfilt` object with the desired structure, and then importing the filter into the block.

Random Source — Better Random Signals and New Option

The Random Source block now outputs much better random signals due to the following algorithmic enhancements:

- **Uses improved random generators** — The block now uses the same random generator algorithms as the current `rand` and `randn` functions. These generators yield much better random signals than the MATLAB Version 4 generators that were previously used by the Random Source block.
- **Better automatic seed generation** — When you opt to specify a single initial seed for a multichannel output, the block automatically generates an initial seed for each channel (using the seed you provide). The block now generates these initial seeds using an improved method that results in better random signals.
- **Better complex random signal generation** — The block now generates complex random values using an improved method that results in better complex random signals.

The Random Source block also now offers a second method of computing Gaussian (normally distributed) random signals based on the central limit theorem. When set to use this new method, the block computes Gaussian random values by adding and scaling uniformly distributed random signals. The block allows you to specify the number of uniform values to sum.

Sine Wave — Accepts Zero and Negative Frequencies

The Sine Wave block now accepts zero and negative frequency values in addition to positive frequency values.

New and Enhanced Demos

You can access all DSP Blockset demos (in the Help browser **Demo** tab) by typing `demo blockset dsp` at the command line. To open the new and enhanced demos, you can also click the links in the following table in the MATLAB Help browser (*not* in a Web browser).

New and Enhanced Demos	Location in DSP Blockset Entry of Help Browser Demo Tab	Enhancement Description
GSM Digital Down Converter	Communications	New
FIR Interpolation	Filtering	These demos now provide a fixed-point version that you can run when you install the Fixed-Point Blockset.
Denoising	Wavelets	
Wavelet Transmultiplexer (WTM)	Wavelets	
Multi-Level PR Filter Bank	Wavelets	Formerly a 1-level filter bank demo, this demo now demonstrates a three-level perfect reconstruction wavelet-based filter bank. This demo also provides a new fixed-point version that you can run when you install the Fixed-Point Blockset.

Audio Blocks Relocated to New Block Library

The four audio blocks, formerly in the DSP Sources and DSP Sinks libraries, are now in the new Windows (WIN32) library (a sublibrary of the new Platform-specific I/O library).

New DSP Blockset Block Libraries

- **Platform-specific I/O** — New block library that contains sublibraries for use with specific platforms such as the Windows operating system. To see the library, type `dsppio`, or type `simulink` and navigate to the library using the Simulink Library Browser.
- **Windows (WIN32)** — Sublibrary of the Platform-specific I/O library. Contains blocks (listed below) for use with 32-bit Windows operating systems. To see the library, type `dspwin32`, or type `simulink` and navigate to the library using the Simulink Library Browser.

Blocks Relocated to the Windows (WIN32) Library

- To Wave File
- To Wave Device
- From Wave File
- From Wave Device


New Options for Event Detection

The following blocks perform an operation when an event-detecting input port (such as a clock or reset port) detects an event:


- Counter
- Cumulative Product
- Cumulative Sum
- Histogram
- Integer Delay
- Maximum
- Mean
- Minimum
- N-Sample Enable
- Queue
- RMS
- Stack
- Standard Deviation
- Variance

You can now set the event-detecting ports of the above blocks to respond to one of the following events:

- **Non-zero sample** — When the input sample is nonzero
- **Rising edge** — When the input does one of the following:
 - Rises from a negative value to a positive value or zero
 - Rises from zero to a positive value, where the rise is not a continuation of a rise from a negative value to zero (see the following figure)



- **Falling edge** — When the input does one of the following:
 - Falls from a positive value to a negative value or zero
 - Falls from zero to a negative value, where the fall is not a continuation of a fall from a positive value to zero (see the following figure)



- **Either edge** — When an input is a **Rising edge** or **Falling edge** (as described above)

Major Bug Fixes

The DSP Blockset 5.0 includes several bug fixes made since Version 4.1. This section describes the particularly important Version 5.0 bug fixes.

If you are viewing these Release Notes in PDF form, please refer to the HTML form of the Release Notes, using either the Help browser or the MathWorks Web site and use the link provided.

If you are upgrading from a release earlier than Release 12.1, then you should see “Major Bug Fixes” on page 4-10.

Upgrading from an Earlier Release

The following topics describe the upgrade issues involved in moving from the DSP Blockset 4.1 to Version 5.0:

- “New Default Setting Enables Boolean Data Type Support” on page 3-19
- “Replaced Filtering Blocks” on page 3-20
- “Wavelet Analysis and Wavelet Synthesis Blocks Replaced” on page 3-20
- “Cumulative Sum Block Behaves Differently” on page 3-21
- “Contiguous Copy Block Obsolete” on page 3-21
- “Audio Blocks Relocated” on page 3-21

If you are upgrading from a version earlier than 4.0, then you should see “Upgrading from an Earlier Release” on page 5-12 of the DSP Blockset 4.0 Release Notes.

New Default Setting Enables Boolean Data Type Support

The Simulink default settings now *enable* Boolean data type support. This allows you to take advantage of the full Boolean data type support in DSP Blockset 5.0.

In some cases, you may want to override the Simulink default and *disable* Boolean support. For instance, for each of the following blocks, the default data type of at least one output has now changed from double precision to Boolean:

- Counter
- Edge Detector
- Event-Count Comparator
- Multiphase Clock
- N-Sample Enable
- Queue
- Stack

If you have a model that uses previous versions of the above blocks, their new default Boolean data type can potentially break your model. If the change in data type does break your model, you can fix this by disabling Boolean support; then the output data type of the blocks will remain double precision, and your model will behave just as it did before.

For more information about disabling Boolean support, see the following topics in the DSP Blockset documentation:

- Steps to disable Boolean support
- The effects of enabling and disabling Boolean support

For more information about the new Boolean data type support in DSP Blockset 5.0, see the following topics:

- “Full Boolean Data Type Support” on page 3-4 — Description of the new full support of the Boolean data type in DSP Blockset 5.0.
- A list of all DSP Blockset blocks that support Boolean data types in the DSP Blockset documentation.

Replaced Filtering Blocks

The new Digital Filter block in the Filter Designs library replaces the following blocks from DSP Blockset 4.1:

- Biquadratic Filter
- Time-Varying Lattice Filter
- Time-Varying Direct-Form II Transpose Filter

Your models that contain these replaced blocks will still work, and you can still access these blocks by typing `dsparch3` at the MATLAB command line.

However, when creating new models, use the new Digital Filter block, which can implement various filters including those that the above three blocks implement: biquadratic direct form II transposed filters, time-varying lattice filters, and time-varying direct form II transposed filters.

See “Digital Filter” on page 3-6 for more information about the new Digital Filter block.

Wavelet Analysis and Wavelet Synthesis Blocks Replaced

The Wavelet Analysis and Wavelet Synthesis blocks, formerly in the Multirate Filters library, are now replaced by new or enhanced blocks as summarized in the following table.

New or Enhanced Block	Replaces...
Dyadic Analysis Filter Bank	Wavelet Analysis block in frame-based operation
Dyadic Synthesis Filter Bank	Wavelet Synthesis block in frame-based operation
Two-Channel Analysis Subband Filter	Wavelet Analysis block in sample-based or frame-based operation
Two-Channel Synthesis Subband Filter	Wavelet Analysis block in sample-based or frame-based operation

You can still access the Wavelet Analysis and Wavelet Synthesis blocks by typing `dspmlti3` at the command line.

For more information about the new and enhanced replacement blocks, see the following topics:

- “Two-Channel Analysis Subband Filter and Two-Channel Synthesis Subband Filter” on page 3-8
- “Dyadic Analysis Filter Bank and Dyadic Synthesis Filter Bank Enhancements” on page 3-11

Cumulative Sum Block Behaves Differently

The Cumulative Sum block now behaves differently when given frame-based inputs and set to sum along columns. In this situation, the block now computes the running sum of each column of a frame-based input, where the running sum is independent of the running sums of previous inputs.

To get the previous behavior for frame-based inputs when set to sum along columns, set the block to sum along channels.

Contiguous Copy Block Obsolete

The Contiguous Copy block, formerly in the Signal Attributes library, is now obsolete. Your models that currently use the block will still work, but you can no longer access the block in the DSP Blockset 5.0 libraries.

Audio Blocks Relocated

The following blocks, formerly in the DSP Sources and DSP Sinks libraries, are now in the new Windows (WIN32) library:

- From Wave Device
- From Wave File
- To Wave Device
- To Wave File

For more information, see “Audio Blocks Relocated to New Block Library” on page 3-15.

DSP Blockset 4.1 Release Notes

New Features	4-2
New Digital Filter Design Block	4-2
Major Individual Block Enhancements	4-2
Blocks with Enhanced Data Type Support	4-5
Blocks with Tunability Enhancements	4-6
Enhancements to Blocks Implemented with S-Functions	4-7
Real-Time Workshop Generated C Code Enhancements	4-8
Changes to Filtering Block Libraries	4-9
Major Bug Fixes	4-10
Real-Time Workshop C Code Generated from DSP Blockset	4-10
Nontunable Block Parameters	4-10
Chirp Block	4-10
Matrix Viewer Block	4-10
Random Source Block	4-11
Stack and Queue Blocks	4-11
Window Function Block	4-11
Upgrading from an Earlier Release	4-12

New Features

This section introduces the new features and enhancements added in the DSP Blockset 4.1 (Release 12.1) since DSP Blockset 4.0 (Release 12.0).

If you are upgrading from a release earlier than Release 12.0, then you should see “New Features” on page 5-2.

The DSP Blockset 4.1 new features are discussed in detail in the following sections:

- “New Digital Filter Design Block” on page 4-2
- “Major Individual Block Enhancements” on page 4-2
- “Blocks with Enhanced Data Type Support” on page 4-5
- “Blocks with Tunability Enhancements” on page 4-6
- “Enhancements to Blocks Implemented with S-Functions” on page 4-7
- “Real-Time Workshop Generated C Code Enhancements” on page 4-8
- “Changes to Filtering Block Libraries” on page 4-9

New Digital Filter Design Block

The new Digital Filter Design block integrates the Filter Design and Analysis Tool graphical user interface (FDATool) with the DSP Blockset.

Double-clicking the block opens FDATool, which you can use to quickly design, import, or directly specify a digital FIR or IIR filter. Using the specified filter, the block filters the input signal and outputs the result.

The Digital Filter Design block replaces many of the blocks from DSP Blockset 4.0 (Release 12). For details, see “Changes to Filtering Block Libraries” on page 4-9.

To implement a filter you have already designed, use the Digital Filter block, introduced in DSP Blockset 5.0 (Release 13).

Major Individual Block Enhancements

The following sections summarize the major individual block enhancements for DSP Blockset 4.1:

- “FFT Block”
- “IFFT Block”

- “Magnitude FFT Block”
- “Overlap-Add FFT Filter and Overlap-Save FFT Filter Blocks”
- “Random Source Block”
- “Sine Wave Block”
- “Unwrap Block”
- “Window Function Block”

FFT Block

- You can now set the block to compute twiddle factors by table lookup or by calling trigonometric math library functions. In table lookup mode, the block precomputes and stores a table that you can optimize for memory or speed. For an N-point FFT, a table optimized for speed yields a length- $3N/4$ table, and a table optimized for memory yields a length- $N/4$ table.
- A new option lets you set the block to output in bit-reversed or linear order. Outputting in bit-reversed order reduces computation time by eliminating the output data descrambling step.
- The block processes real-valued inputs using more efficient algorithms.
- The block generates smaller Real-Time Workshop C code with improved run-time efficiency through use of in-place algorithms.
- The block now supports single-precision (32-bit) floating-point input and output signals (in table lookup mode) for both simulation and Real-Time Workshop C code generation.

For more information, see the FFT block reference page.

IFFT Block

- You can now set the block's twiddle factor computation method as in the FFT block (see the earlier FFT block enhancement description).
- A new option lets you provide inputs in both linear and bit-reversed order. Using inputs in bit-reversed order reduces block computation time by eliminating the initial input data scrambling step.
- You can now explicitly specify conjugate-symmetric input signals to significantly increase processing efficiency and to get a real-valued output signal.

- You can now skip normalization by the IFFT length, N , when you do not need to output a normalized signal, increasing processing efficiency.
- The block generates smaller Real-Time Workshop C code with improved run-time efficiency through use of in-place algorithms.
- The block now supports single-precision (32-bit) floating-point input and output signals (in table lookup mode) for both simulation and Real-Time Workshop C code generation.

For more information, see the IFFT block reference page.

Magnitude FFT Block

- You can now set the block to compute the magnitude FFT or magnitude squared FFT
- The block uses the new, more efficient FFT block algorithms.

For more information, see the Magnitude FFT block reference page.

Overlap-Add FFT Filter and Overlap-Save FFT Filter Blocks

By using the enhanced FFT and IFFT blocks, the Overlap-Add FFT Filter and Overlap-Save FFT Filter blocks are more efficient. (Both blocks now skip data descrambling and scrambling operations by processing data in bit-reversed order, and use specialized, more efficient algorithms for real-valued input signals.)

Random Source Block

- You can now set the repeatability of the block output to **Not repeatable**, **Repeatable**, or **Specify seed**. The default mode is **Not repeatable**, so that when you add new Random Source blocks from the block library to a model, the blocks automatically generate different outputs (without requiring you to specify a seed).
- The block now uses Simulink run-time parameters, greatly enhancing its Real-Time Workshop generated C code (see “Enhancements to Blocks Implemented with S-Functions” on page 4-7).

Sine Wave Block

You can now optimize the Sine Wave block’s table lookup computation method for speed or memory. For speed optimization, the block uses a full-length table, while for memory optimization, it uses a 1/4-length table.

Unwrap Block

You can now set the Unwrap block to phase unwrap across successive inputs for both frame-based and sample-based input signals.

Window Function Block

- The Window Function block now generates smaller, more efficient Real-Time Workshop C code by using run-time parameters (see “Enhancements to Blocks Implemented with S-Functions” on page 4-7).
- The block now supports single-precision (32-bit) floating-point input and output signals.

Blocks with Enhanced Data Type Support

Many blocks now support all Simulink built-in data types, as well as the fixed-point data type and properly defined Simulink custom data types in both simulation and in Real-Time Workshop C code generation. To see which data types a particular block supports, check the “Supported Data Types” section of its reference page.

The data signal input and output ports (noncontrol input and output ports) of the following blocks now support all built-in, fixed-point, and other properly defined Simulink custom data types:

- Buffer
- Check Signal Attributes
- Contiguous Copy
- Convert 1-D to 2-D
- Convert 2-D to 1-D
- Delay Line
- Display
- Downsample
- Extract Diagonal
- Extract Triangular Matrix
- Flip
- Frame Status Conversion
- Inherit Complexity
- Integer Delay
- Matrix Viewer
- Multiport Selector
- Pad
- Permute Matrix (also, index input port accepts signed and unsigned integer and double- and single-precision floating-point)
- Repeat
- Sample and Hold
- Signal To Workspace
- Spectrum Scope
- Submatrix
- Time Scope
- Toeplitz
- Transpose
- Triggered Delay line
- Triggered To Workspace
- Unbuffer
- Upsample
- Variable Integer Delay
- Variable Selector (also, index input port accepts signed and unsigned integer and double- and single-precision floating-point)
- Vector Scope
- Zero Pad

The data signal input and output ports (noncontrol input and output ports) of the following blocks now support all Simulink built-in data types:

- Constant Diagonal Matrix
- DSP Constant
- Signal From Workspace
- Triggered Signal From Workspace

Blocks with Tunability Enhancements

The following blocks have enhanced tunability:

- Chirp — **Target time** parameter is now tunable.
- Counter — **Maximum count** parameter is now tunable.
- Mean — **Reset port** parameter is now tunable.
- Pad — **Value** parameter is now tunable.

Enhancements to Blocks Implemented with S-Functions

Many of the DSP Blockset blocks are S-function blocks (implemented with Simulink S-functions). The following sections summarize some of the major DSP Blockset 4.1 enhancements that improve S-function block performance and help you to write better S-functions.

Use of Simulink Run-Time Parameters

Many S-function blocks now generate better optimized Real-Time Workshop C code by using Simulink run-time parameters (RTPs) for both mask dialog and internal parameters. Blocks that use RTPs include those with filter coefficient parameters and initial condition parameters.

Better Memory Management for Simulation and Code Generation

Memory management enhancements for S-function block simulation and code generation now provide simulation code requiring less memory, and smaller Real-Time Workshop generated C code that is more efficient at run-time. Memory management enhancements include the use of contiguous input and output arrays, reusable inputs, overwriteable arrays, and in-place algorithms.

New S-Function Simulation Support Directories

Various extensible C-callable library functions, macros, and definitions are now included in the following directories:

- `toolbox/dspblks/include` — header files (prototypes and definitions)
- `toolbox/dspblks/src/sim` — simulation library source code
- `toolbox/dspblks/lib` — prebuilt library (`.lib`) files for certain combinations of platforms and compilers only

Real-Time Workshop Generated C Code Enhancements

DSP Blockset 4.1 enhancements that provide better Real-Time Workshop generated C code include the following:

- DSP Blockset can now build and link C-callable run-time libraries, providing for smaller, more efficient Real-Time Workshop generated C code.
- The use of run-time parameters in blocks implemented with S-functions (see “Enhancements to Blocks Implemented with S-Functions” on page 4-7) provides for the following Real-Time Workshop generated C code enhancements for blocks implemented using S-functions:
 - Parameter values are organized in a common structure.
 - Parameter values are located in a common header file (for example, `<model>_prm.h`).
 - Redundant copies of parameter values are reused or “pooled” in `<model>_prm.h` (when there are multiple instances of a block with the same run-time parameter values).

Changes to Filtering Block Libraries

The new **Filter Designs** block library in DSP Blockset 4.1 replaces the old **Filter Structures** and **Filter Designs** block libraries in DSP Blockset 4.0, and contains the following blocks:

- Analog Filter Design
- Biquadratic Filter
- Digital Filter Design
- Direct-Form II Transpose Filter
- Filter Realization Wizard
- Overlap-Add FFT Filter
- Overlap-Save FFT Filter
- Time-Varying Lattice Filter
- Time-Varying Direct-Form II Transpose Filter

The new Digital Filter Design block in the **Filter Designs** block library (see “New Digital Filter Design Block” on page 4-2) replaces the following DSP Blockset 4.0 blocks:

- Digital FIR Filter Design
- Digital FIR Raised Cosine Filter Design
- Digital IIR Filter Design
- Least Squares FIR Filter Design
- Remez FIR Filter Design

Your models that contain these replaced blocks will still work, but they are no longer accessible in the Filter Designs library. You can still access these blocks by typing `dspddes3` at the MATLAB command line, but you should use the Digital Filter Design block to design and implement filters in your new models.

Note The Digital Filter Design block allows you to design a filter, and then implement it. To implement a filter you already designed, use the Digital Filter block, introduced in DSP Blockset 5.0 (Release 13).

Major Bug Fixes

The following sections describe some of the major DSP Blockset 4.1 bug fixes:

- “Real-Time Workshop C Code Generated from DSP Blockset”
- “Nontunable Block Parameters”
- “Chirp Block”
- “Matrix Viewer Block”
- “Random Source Block”
- “Stack and Queue Blocks”
- “Window Function Block”

Real-Time Workshop C Code Generated from DSP Blockset

- Real-Time Workshop C code generated from the blockset now uses the `sizeof` function rather than hard-coding word sizes for nonstandard code generation targets (such as those that do not treat characters as 8-bit bytes).
- The generated C code for most blocks no longer generates compiler warnings for most supported targets.

Nontunable Block Parameters

All nontunable block parameters are now uneditable in the Simulink mask UI during simulations.

Chirp Block

The Chirp block now has correct behavior in bidirectional sweep mode, and correctly interprets target frequency and sweep time parameters.

Matrix Viewer Block

The Matrix Viewer block now displays the color bar.

Random Source Block

The Random Source block seed initialization better supports multiple copies of the block in one Simulink model.

Also, the block no longer sets the seed of the MATLAB random number generator function during block initialization.

Stack and Queue Blocks

The Stack and Queue blocks now correctly handle simultaneously triggered control ports (such as the Push and Pop ports).

Window Function Block

The Window Function block now errors out for non-floating-point inputs to avoid possible segmentation violations.

Upgrading from an Earlier Release

There are no issues for upgrading from DSP Blockset 4.0 (Release 12) to DSP Blockset 4.1 (Release 12.1).

For information about upgrading from an earlier version than DSP Blockset 4.0, see “Upgrading from an Earlier Release” on page 5-12.

DSP Blockset 4.0 Release Notes

New Features	5-2
Matrix Support	5-2
Frame Support	5-4
New and Enhanced Blocks	5-5
Library Reorganization	5-7
Upgrading from an Earlier Release	5-12
Adding Release 12 Blocks to Release 11 Models	5-12

New Features

This section introduces the new features and enhancements added in the DSP Blockset 4.0 since the DSP Blockset 3.1 (Release 11.0).

Version 4.0 of the DSP Blockset offers complete support for the Simulink 4.0 enhancements that provide seamless propagation and processing of both matrix and frame-based signals. A number of new blocks are also provided.

This section is organized into the following subsections:

- “Matrix Support” on page 5-2
- “Frame Support” on page 5-4
- “New and Enhanced Blocks” on page 5-5
- “Library Reorganization” on page 5-7

Matrix Support

Matrix support is now provided natively within Simulink, which allows the DSP Blockset to generate and process matrix signals in a much more natural manner than was previously possible.

Generating Matrix Signals

Matrix signals can now be generated in the same way as vector or scalar signals, using appropriate source blocks such as Signal From Workspace or DSP Constant. Where you would have previously specified a vector or scalar, you can now use standard MATLAB notation to specify a matrix. For example, enter [1 2 3; 4 5 6] in the **Constant value** parameter of the DSP Constant block to generate the 2-by-3 output matrix.

$$\begin{bmatrix} 1 & 2 & 3 \\ 4 & 5 & 6 \end{bmatrix}$$

When **Signal dimensions** is selected from the model window **Format** menu, Simulink displays the dimensions of an M-by-N matrix signal as a pair of bracketed integers, [MxN]. Simulink *does not display* any size information for a scalar signal. Dimension information for a signal can also be displayed in a model by attaching a Probe block with **Probe signal dimensions** selected.

Row vectors and column vectors are matrices with $M=1$ or $N=1$, respectively. These are generated by the DSP Constant block when a vector is specified in the **Constant value** parameter and the **Interpret vector parameters as 1-D** check box is *not* selected.

In addition, Simulink recognizes one-dimensional (1-D) vectors, which are ordered lists of values. These are generated by the DSP Constant block when a vector is specified in the **Constant value** parameter and the **Interpret vector parameters as 1-D** check box is selected. When **Signal dimensions** is selected from the model window **Format** menu, Simulink displays the size of a 1-D vector signal as an unbracketed integer. For convenience, DSP Blockset blocks treat 1-D vectors as column vectors for most operations.

Processing Matrix Signals

The most noticeable benefit of the new matrix enhancements is that you no longer need to manually specify the size of matrix inputs to a block. All DSP Blockset blocks now automatically detect input dimensions, and will generate an error if those dimensions are not appropriate for the specific operation.

Since input dimensions are detected automatically by new (Version 4.0) blocks, a matrix output of an older block may need to be altered before you use it as an input to a new block, and vice versa. See “Adding Release 12 Blocks to Release 11 Models” on page 5-12 for more information.

The interpretation of sample-based and frame-based matrices is the same as in previous releases. An M -by- N sample-based matrix represents $M \cdot N$ independent channels, each containing one sample. An M -by- N frame-based matrix represents M consecutive samples from each of N independent channels. That is, each column of a frame-based matrix represents M consecutive samples from a single channel.

Frame Support

Support for frame-based signals is also now provided natively within Simulink, which allows for straightforward propagation of frame-based data throughout a model.

Generating Frame-Based Signals

Frame-based signals are generated in much the same way that they were in previous DSP Blockset releases. In constant blocks such as DSP Constant or Constant Diagonal Matrix, the **Frame-based output** check box confers frame-based status when selected. In other source blocks, such as Signal From Workspace, Chirp, and Random Source, the output is frame based whenever the **Samples per frame** setting is greater than 1.

Note that 1-D vectors cannot be frame based. See the DSP Constant block reference for information about the interaction of the **Frame-based output** and **Interpret vector parameters as 1-D** parameters.

Processing Frame-Based Signals

Frame-based status is now propagated automatically throughout a model. Most blocks do not change the frame status of a signal; frame-based signals remain frame based, and sample-based signals remain sample based. The exceptions to this rule are blocks, like Buffer and Frame Status Conversion, that are specifically intended to alter the frame status of a signal.

Since frame status is now automatically detected by the new (Version 4.0) blocks, a frame-based output from an older block may need to be altered before you use it as an input to a new block, and vice versa. See “Adding Release 12 Blocks to Release 11 Models” on page 5-12 for more information.

As mentioned above, the interpretation of sample-based and frame-based matrices is the same as in previous releases. An M-by-N sample-based matrix represents M*N independent channels, each containing one sample. An M-by-N frame-based matrix represents M consecutive samples from each of N independent channels. For convenience, certain vector-oriented blocks such as Autocorrelation treat sample-based 1-by-N matrices (i.e., row vectors) as N-by-1 matrices (i.e., column vectors). See the documentation for the particular block in which you are interested.

Simulink displays sample-based signals using a single line, \rightarrow , and frame-based signals using a double line, \Rightarrow . The sample period (T_s) of a

sample-based signal, or the frame period (T_f) of a frame-based signal, can be displayed by connecting a Probe block to the line. As always, the sample period of a frame-based signal is T_f / M , where M is the signal's frame size (i.e., the number of rows in the frame-based M-by-N matrix).

New and Enhanced Blocks

Table 5-1 lists the blocks that are new in Version 4.0, as well as those (*) that received substantial enhancements above and beyond the general upgrade for matrix and frame support. Library levels are separated by a forward slash.

Table 5-1: New and Enhanced Blocks in the DSP Blockset 4.0

Block Library	Block Name	Description
DSP Sources	Chirp*	Generate a swept-frequency cosine. Version 4.0 adds bidirectional sweep.
	Constant Ramp	Generate a ramp signal with length based on input dimensions.
	Window Function*	Compute a window, and/or apply a window to an input signal. Version 4.0 can compute user-defined windows.
DSP Sinks	Signal To Workspace	Replaces To Workspace.
	Spectrum Scope	Replaces FFT Frame Scope and Buffered FFT Frame Scope.
	Vector Scope	Replaces Time Frame Scope, User-Defined Frame Scope, and Frequency Frame Scope.
Estimation / Linear Prediction	Autocorrelation LPC	Determine the coefficients of an Nth-order forward linear predictor.
Math Functions / Matrices and Linear Algebra / Linear System Solvers	SVD Solver	Solve the equation $AX = B$ using singular value decomposition.
Math Functions / Matrices and Linear Algebra / Matrix Factorizations	Singular Value Decomposition	Compute the singular value decomposition of a matrix.
Math Functions / Matrices and Linear Algebra / Matrix Inverses	Cholesky Inverse	Compute the inverse of a Hermitian positive definite matrix using Cholesky factorization.
	LDL Inverse	Compute the inverse of a Hermitian positive definite matrix using LDL factorization.
	LU Inverse	Compute the inverse of a square matrix using LU factorization.
	Pseudoinverse	Compute the Moore-Penrose pseudoinverse.
Math Functions / Matrices and Linear Algebra / Matrix Operations	Identity Matrix	Generate a matrix with ones on the main diagonal and zeros elsewhere.
	Submatrix*	Select a subset of elements (submatrix) from a matrix input. Version 4.0 offers a major redesign of the block's interface.

Table 5-1: New and Enhanced Blocks in the DSP Blockset 4.0 (Continued)

Block Library	Block Name	Description
Math Functions / Polynomial Functions	Least Squares Polynomial Fit	Compute the coefficients of the polynomial that best fits the input data in a least-squares sense.
	Polynomial Stability Test	Determine whether all roots of the input polynomial are inside the unit circle using the Schur-Cohn algorithm.
Signal Management / Buffers	Buffer*	Rebuffer the input sequence to a smaller or larger frame size. In Version 4.0, the Buffer block incorporates all the capabilities of the former Rebuffer block. See “Minor Enhancements” below for more information.
	Delay Line	Rebuffer a sequence of inputs with a one-sample shift. Previously called Shift Register.
	Triggered Delay Line	Rebuffer a sequence of inputs with a one-sample shift. Previously called Triggered Shift Register.
Signal Management / Indexing	Multiport Selector	Distribute rows or columns of an input to multiple output ports.
Signal Management / Signal Attributes	Check Signal Attributes	Generate an error if input attributes differ from (or match) those specified.
	Convert 1-D to 2-D	Reshape a 1-D or 2-D input to a 2-D matrix with the specified dimensions.
	Convert 2-D to 1-D	Convert a 2-D matrix input to a 1-D vector.
	Frame Status Conversion	Specify the frame status of the output, sample-based or frame-based.
Signal Operations	Pad	Alter the input size by padding or truncating rows and/or columns.
Simulink / Signals & Systems	Matrix Concatenation	Concatenate inputs horizontally or vertically.

Minor Enhancements

Rowwise Operations. A number of blocks were enhanced to operate along both the row and column dimensions of inputs. Among the improved blocks are Zero Pad, Flip, Difference, and Cumulative Sum. All these blocks now allow you to select **Rows** or **Columns** as the dimension along which to operate.

Buffers Library Reorganization. The Buffers library has undergone a minor reorganization. The Buffer block now incorporates all the capabilities of the former Rebuffer block, which has been removed. The former Shift Register and Triggered Shift Register blocks have also been renamed to Delay Line and Triggered Delay Line, respectively.

Library Reorganization

The DSP Blockset libraries have been reorganized for clarity and accessibility. The revised library hierarchy is shown below:

- DSP Sinks
- DSP Sources
- Estimation
 - Linear Prediction
 - Parametric Estimation
 - Power Spectrum Estimation
- Filtering
 - Adaptive Filters
 - Filter Designs
 - Filter Structures
 - Multirate Filters
- Math Functions
 - Math Operations
 - Matrices and Linear Algebra
 - Linear System Solvers
 - Matrix Factorizations
 - Matrix Inverses
 - Matrix Operations
 - Polynomial Functions
- Quantizers
- Signal Management
 - Buffers
 - Indexing
 - Signal Attributes
 - Switches and Counters
- Signal Operations
- Statistics
- Transforms

Use the Simulink Library Browser to access the blockset directly through this hierarchical library list.

As a result of the reorganization, a number of existing blocks have been moved to new locations. Table 5-2 below lists the changes.

Table 5-2: New Block Locations in Version 4.0

Old Block Name	Old Library Location	New Block Name	New Library Location
Analog Filter Design	Filtering / Filter Designs	same	Filtering / Filter Structures
Analytic Signal	General DSP / Signal Operations	same	Transforms
Autocorrelation	Math Functions / Vector Functions	same	Statistics
Backward Substitution	Math Functions / Linear Algebra	same	Math Functions / Matrices and Linear Algebra / Linear System Solvers
Biquadratic Filter	Filtering / Filter Realizations	same	Filtering / Filter Structures
Buffered FFT Frame Scope	DSP Sinks	Spectrum Scope	same
Cholesky Factorization	Math Functions / Linear Algebra	same	Math Functions / Matrices and Linear Algebra / Matrix Factorizations
Cholesky Solver	Math Functions / Linear Algebra	same	Math Functions / Matrices and Linear Algebra / Linear System Solvers
Commutator	General DSP / Switches and Counters	obsolete	obsolete
Complex Exponential	Math Functions / Elementary Functions	same	Math Functions / Math Operations
Constant Diagonal Matrix	DSP Sources, Math Functions / Matrix Functions	same	Math Functions / Matrices and Linear Algebra / Matrix Operations
Contiguous Copy	Math Functions / Elementary Functions	same	Signal Management / Signal Attributes
Convert Complex DSP To Simulink	Math Functions / Elementary Functions	obsolete	obsolete
Convert Complex Simulink To DSP	Math Functions / Elementary Functions	obsolete	obsolete
Convolution	Math Functions / Vector Functions	same	Signal Operations
Correlation	Math Functions / Vector Functions	same	Statistics
Create Diagonal Matrix	Math Functions / Matrix Functions	same	Math Functions / Matrices and Linear Algebra / Matrix Operations
Cumulative Sum	Math Functions / Vector Functions	same	Math Functions / Math Operations

Table 5-2: New Block Locations in Version 4.0 (Continued)

Old Block Name	Old Library Location	New Block Name	New Library Location
dB	Math Functions / Elementary Functions	dB Conversion	Math Functions / Math Operations
dB Gain	Math Functions / Elementary Functions	same	Math Functions / Math Operations
Detrend	General DSP / Signal Operations	same	Statistics
Difference	Math Functions / Vector Functions	same	Math Functions / Math Operations
Direct-Form II Transpose Filter	Filtering / Filter Realizations	same	Filtering / Filter Structures
Discrete Constant	DSP Sources	DSP Constant	same
Distributor	General DSP / Switches and Counters	obsolete	obsolete
Downsample	General DSP / Signal Operations	same	Signal Operations
Extract Diagonal	Math Functions / Matrix Functions	same	Math Functions / Matrices and Linear Algebra / Matrix Operations
Extract Triangular Matrix	Math Functions / Matrix Functions	same	Math Functions / Matrices and Linear Algebra / Matrix Operations
FFT Frame Scope	DSP Sinks	Spectrum Scope	same
Filter Realization Wizard	Filtering / Filter Realizations	same	Filtering / Filter Structures
Flip	Math Functions / Vector Functions	same	Signal Management / Indexing
Forward Substitution	Math Functions / Linear Algebra	same	Math Functions / Matrices and Linear Algebra / Linear System Solvers
Frequency Frame Scope	DSP Sinks	Vector Scope	same
Inherit Complexity	Math Functions / Elementary Functions	same	Signal Management / Signal Attributes
Integer Delay	General DSP / Signal Operations	same	Signal Operations
LDL Factorization	Math Functions / Linear Algebra	same	Math Functions / Matrices and Linear Algebra / Matrix Factorizations
LDL Solver	Math Functions / Linear Algebra	same	Math Functions / Matrices and Linear Algebra / Linear System Solvers
Levinson Solver	Math Functions / Linear Algebra	same	Math Functions / Matrices and Linear Algebra / Linear System Solvers
LPC	General DSP / Signal Operations	Autocorrelation LPC	Estimation / Linear Prediction
LU Factorization	Math Functions / Linear Algebra	same	Math Functions / Matrices and Linear Algebra / Matrix Factorizations

Table 5-2: New Block Locations in Version 4.0 (Continued)

Old Block Name	Old Library Location	New Block Name	New Library Location
LU Solver	Math Functions / Linear Algebra	same	Math Functions / Matrices and Linear Algebra / Linear System Solvers
Matrix 1-Norm	Math Functions / Matrix Functions	same	Math Functions / Matrices and Linear Algebra / Matrix Operations
Matrix Constant	DSP Sources, Math Functions / Matrix Functions	DSP Constant	DSP Sources
Matrix From Workspace	DSP Sources, Math Functions / Matrix Functions	From Workspace	DSP Sources
Matrix Multiplication	Math Functions / Matrix Functions	Matrix Multiply	Math Functions / Matrices and Linear Algebra / Matrix Operations
Matrix Product	Math Functions / Matrix Functions	same	Math Functions / Matrices and Linear Algebra / Matrix Operations
Matrix Scaling	Math Functions / Matrix Functions	same	Math Functions / Matrices and Linear Algebra / Matrix Operations
Matrix Square	Math Functions / Matrix Functions	same	Math Functions / Matrices and Linear Algebra / Matrix Operations
Matrix Sum	Math Functions / Matrix Functions	same	Math Functions / Matrices and Linear Algebra / Matrix Operations
Matrix To Workspace	DSP Sinks, Math Functions / Matrix Functions	To Workspace	DSP Sinks
Multiphase Clock	DSP Sources, General DSP / Switches and Counters	same	DSP Sources
Normalization	Math Functions / Vector Functions	same	Math Functions / Math Operations
Overlap-Add FFT Filter	Filtering / Filter Realizations	same	Filtering / Filter Structures
Overlap-Save FFT Filter	Filtering / Filter Realizations	same	Filtering / Filter Structures
Partial Unbuffer	General DSP / Buffers	Buffer / Unbuffer	same
Permute Matrix	Math Functions / Matrix Functions	same	Math Functions / Matrices and Linear Algebra / Matrix Operations
Polynomial Evaluation	Math Functions / Elementary Functions	same	Math Functions / Polynomial Functions
QR Factorization	Math Functions / Linear Algebra	same	Math Functions / Matrices and Linear Algebra / Matrix Factorizations
QR Solver	Math Functions / Linear Algebra	same	Math Functions / Matrices and Linear Algebra / Linear System Solvers
Rebuffer	General DSP / Buffers	Buffer/Unbuffer	same

Table 5-2: New Block Locations in Version 4.0 (Continued)

Old Block Name	Old Library Location	New Block Name	New Library Location
Reciprocal Condition	Math Functions / Linear Algebra	same	Math Functions / Matrices and Linear Algebra / Matrix Operations
Repeat	General DSP / Signal Operations	same	Signal Operations
Reshape	Math Functions / Matrix Functions	same	Simulink / Signals & Systems
Sample and Hold	General DSP / Switches and Counters	same	Signal Operations
Shift Register	General DSP / Buffers	Delay Line	same
Submatrix	Math Functions / Matrix Functions	same	Math Functions / Matrices and Linear Algebra / Matrix Operations
Time Frame Scope	DSP Sinks	Vector Scope	same
Time-Varying Direct-Form II Transpose Filter	Filtering / Filter Realizations	same	Filter Structures
Time-Varying Lattice Filter	Filtering / Filter Realizations	same	Filter Structures
Toeplitz	Math Functions / Matrix Functions	same	Math Functions / Matrices and Linear Algebra / Matrix Operations
Transpose	Math Functions / Matrix Functions	same	Math Functions / Matrices and Linear Algebra / Matrix Operations
Triggered Matrix To Workspace	DSP Sinks	Triggered To Workspace	same
Triggered Shift Register	General DSP / Buffers	Triggered Delay Line	same
Unwrap	Math Functions / Vector Functions	same	Signal Operations
Upsample	General DSP / Signal Operations	same	Signal Operations
User-Defined Frame Scope	DSP Sinks	Vector Scope	same
Variable Fractional Delay	General DSP / Signal Operations	same	Signal Operations
Variable Integer Delay	General DSP / Signal Operations	same	Signal Operations
Variable Selector	Math Functions / Elementary Functions	same	Signal Management / Indexing
Window Function	DSP Sources, General DSP / Signal Operations	same	Signal Operations
Zero Pad	General DSP / Signal Operations	same	Signal Operations

Upgrading from an Earlier Release

This section describes the upgrade issues involved in moving from the DSP Blockset 3.1 to the DSP Blockset 4.0.

Adding Release 12 Blocks to Release 11 Models

All DSP Blockset Version 4.0 blocks support the Simulink 4.0 matrix and frame enhancements. Thus, when you add new (Version 4.0) blocks to a model containing older blocks, some of the signals may need to be altered. Otherwise, an older block may not correctly recognize the output from a new block, and vice versa. See “Using Version 4.0 Blocks with Blocks from Earlier Versions” “Checking Block Versions” and “Finding Replacement Blocks” below for details.

Using Version 4.0 Blocks with Blocks from Earlier Versions

Input dimension and frame status are detected automatically by new (Version 4.0) blocks but not by older blocks from previous releases. Thus, when both new and older blocks are used in a model, some signals may need to be passed through conversion blocks so the dimension and frame status of signals are recognized by their receiving blocks.

Using Outputs from Older Blocks as Inputs to New Blocks. All outputs of blocks from previous releases are 1-D vectors. You can use an output of an older block as an input to a new block without altering the signal. In this case, the new block will usually treat the 1-D input vector as a sample-based 2-D column vector (check the documentation for the particular block in which you are interested). You can also change the 1-D output of an older block to a 2-D sample- or frame-based matrix before feeding it into a new block: simply insert the Convert 1-D to 2-D block in the DSP Blockset Signal Attributes library. See the documentation for the Convert 1-D to 2-D block for more information.

Using Outputs from New Blocks as Inputs to Older Blocks. Older blocks can only accept 1-D inputs. To use an output from a new block as an input to an older block, pass the new output through the Convert 2-D to 1-D block found in the DSP Blockset Signal Attributes library. You can set the frame status and dimensions of the resulting 1-D signal in the parameters dialog box of the older block. See the documentation for the Convert 2-D to 1-D block for more information.

Checking Block Versions

When you begin adding Version 4.0 blocks to an older model, use the `dsp_links` function to check the versions of all blocks in that model. When you type

```
dsp_links
```

at the command line, the blocks in current model are color coded to reflect the version of the DSP Blockset to which they are linked. By default, Version 4.0 blocks are displayed in green. If the color coding reveals that a Version 4.0 block is providing the input to a Version 3 or Version 2 block (displayed in yellow or red by default), the older block should be replaced with a current version. Alternatively, you can use conversion blocks as described previously in “Using Version 4.0 Blocks with Blocks from Earlier Versions” on page 5-12.

Finding Replacement Blocks

In most cases, you can simply replace the older block with the current block of the same name. In general, you should open the block’s dialog box and verify that the settings are correct for the intended operation. (Many block dialogs have undergone minor refinements.)

In certain cases, a block may have changed name or location in Version 4.0. If you cannot find the block you are looking for, check Table 5-2 to see if it may have been renamed or relocated.

